

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250424

Luminaire Tested: **LD8B120D010 ER8B120935 8LBN0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250424
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B120D010 ER8B120935 8LBN0B
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 3500 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6209.1 lumens
Efficiency: N/A
Efficacy: 52.5 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 118.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250424

CATALOG NUMBER: LD8B120D010 ER8B120935 8LBN0B

Luminous Intensity Polar Plot





TEST NUMBER: P250424

CATALOG NUMBER: LD8B120D010 ER8B120935 8LBNOB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72		79	75	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	305939
5°	301050
10°	267477
15°	220643
20°	185827
25°	156735
30°	117353
35°	66416
40°	26262
45°	7052
50°	1353
55°	0
60°	197
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P250424

CATALOG NUMBER: LD8B120D010 ER8B120935 8LBN0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	890.6	14.3
10°-20°	1935.8	31.2
20°-30°	2078.2	33.5
30°-40°	1123.2	18.1
40°-50°	175.3	2.8
50°-60°	4.8	0.1
60°-70°	1.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4904.6	79.0
0°-40°	6027.8	97.1
0°-60°	6207.9	100.0
0°-90°	6209.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6209.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9921	
5°	9726	891
15°	6912	1936
25°	4607	2078
35°	1764	1123
45°	162	175
55°	0	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250424

CATALOG NUMBER: LD8B120D010 ER8B120935 8LBNOB

CANDELA DISTRIBUTION (FULL):

0°	
0°	9921.4
1°	9940.2
2°	9930.9
3°	9896.9
4°	9831.5
5°	9725.7
6°	9580.0
7°	9384.0
8°	9138.7
9°	8856.3
10°	8542.3
11°	8212.9
12°	7871.3
13°	7529.9
14°	7212.7
15°	6911.5
16°	6635.0
17°	6367.8
18°	6119.3
19°	5886.6
20°	5662.8
21°	5445.3
22°	5240.1
23°	5035.4
24°	4821.1
25°	4606.6
26°	4389.1
27°	4140.7
28°	3867.2
29°	3588.0
30°	3295.8
31°	2982.2
32°	2668.2
33°	2357.6
34°	2043.9
35°	1764.3
37.5°	1127.6
40°	652.4
42.5°	348.0
45°	161.7
47.5°	87.2
50°	28.2
52.5°	3.2
55°	0.0
57.5°	3.2



TEST NUMBER: P250424

CATALOG NUMBER: LD8B120D010 ER8B120935 8LBN0B

CANDELA DISTRIBUTION (continued):

	0°
60°	3.2
62.5°	0.0
65°	0.0
67.5°	3.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)