

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247077

Luminaire Tested: **LD8B120D010 ER8B120935 8LBW0LI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P247077  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25264)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B120D010 ER8B120935 8LBW0LI  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
90 CRI 3500 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11200.0 lumens  
Efficiency: N/A  
Efficacy: 94.7 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.22  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 118.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P247077

CATALOG NUMBER: LD8B120D010 ER8B120935 8LBW0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P247077

CATALOG NUMBER: LD8B120D010 ER8B120935 8LBW0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	94	92
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75
4	93	84	78	73	91	83	77	72	81	75	71	79	74	70	77	73	70	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51
8	72	61	54	49	71	60	54	49	59	53	49	58	52	48	57	52	48	47
9	68	56	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43
10	64	53	46	41	63	52	46	41	51	45	41	50	45	41	50	45	41	39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	192721
5°	196481
10°	204909
15°	216487
20°	224601
25°	226233
30°	215535
35°	190114
40°	153259
45°	108809
50°	65397
55°	29461
60°	7598
65°	1642
70°	811
75°	536
80°	266
85°	0



TEST NUMBER: P247077

CATALOG NUMBER: LD8B120D010 ER8B120935 8LBW0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	612.3	5.5
10°-20°	1917.2	17.1
20°-30°	3032.0	27.1
30°-40°	3115.4	27.8
40°-50°	1932.6	17.3
50°-60°	547.9	4.9
60°-70°	37.0	0.3
70°-80°	5.0	0.0
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5561.5	49.7
0°-40°	8677.0	77.5
0°-60°	11157.4	99.6
0°-90°	11200.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11200.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6250	
5°	6348	612
15°	6781	1917
25°	6649	3032
35°	5050	3115
45°	2495	1933
55°	548	548
65°	22	37
75°	4	5
85°	0	1
90°	0	



TEST NUMBER: P247077

CATALOG NUMBER: LD8B120D010 ER8B120935 8LBW0LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6249.8
2.5°	6261.8
5°	6347.5
7.5°	6448.1
10°	6544.1
12.5°	6662.7
15°	6781.3
17.5°	6848.8
20°	6844.4
22.5°	6778.3
25°	6649.2
27.5°	6415.0
30°	6053.2
32.5°	5577.3
35°	5050.3
37.5°	4454.4
40°	3807.3
42.5°	3134.6
45°	2495.1
47.5°	1900.7
50°	1363.2
52.5°	917.3
55°	548.0
57.5°	282.3
60°	123.2
62.5°	49.6
65°	22.5
67.5°	13.5
70°	9.0
72.5°	6.1
75°	4.5
77.5°	3.0
80°	1.5
82.5°	1.5
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)