

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247081

Luminaire Tested: **LD8B120D010 ER8B120940 8LBW0LI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P247081  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25264)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B120D010 ER8B120940 8LBW0LI  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
90 CRI 4000 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11697.0 lumens  
Efficiency: N/A  
Efficacy: 98.9 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.22  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 118.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P247081

CATALOG NUMBER: LD8B120D010 ER8B120940 8LBW0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P247081

CATALOG NUMBER: LD8B120D010 ER8B120940 8LBW0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	94	92
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75
4	93	84	78	73	91	83	77	72	81	75	71	79	74	70	77	73	70	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51
8	72	61	54	49	71	60	54	49	59	53	49	58	52	48	57	52	48	47
9	68	56	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43
10	64	53	46	41	63	52	46	41	51	45	41	50	45	41	50	45	41	39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	201275
5°	205201
10°	214002
15°	226093
20°	234567
25°	236274
30°	225102
35°	198551
40°	160062
45°	113641
50°	68294
55°	30768
60°	7931
65°	1715
70°	847
75°	560
80°	284
85°	0



TEST NUMBER: P247081

CATALOG NUMBER: LD8B120D010 ER8B120940 8LBW0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	639.5	5.5
10°-20°	2002.3	17.1
20°-30°	3166.5	27.1
30°-40°	3253.7	27.8
40°-50°	2018.3	17.3
50°-60°	572.2	4.9
60°-70°	38.7	0.3
70°-80°	5.2	0.0
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5808.3	49.7
0°-40°	9062.0	77.5
0°-60°	11652.5	99.6
0°-90°	11697.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11697.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6527	
5°	6629	639
15°	7082	2002
25°	6944	3167
35°	5274	3254
45°	2606	2018
55°	572	572
65°	24	39
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P247081

CATALOG NUMBER: LD8B120D010 ER8B120940 8LBW0LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6527.2
2.5°	6539.7
5°	6629.2
7.5°	6734.2
10°	6834.5
12.5°	6958.4
15°	7082.2
17.5°	7152.7
20°	7148.1
22.5°	7079.1
25°	6944.3
27.5°	6699.7
30°	6321.9
32.5°	5824.8
35°	5274.4
37.5°	4652.0
40°	3976.3
42.5°	3273.7
45°	2605.9
47.5°	1985.0
50°	1423.6
52.5°	958.1
55°	572.3
57.5°	294.8
60°	128.6
62.5°	51.8
65°	23.5
67.5°	14.1
70°	9.4
72.5°	6.3
75°	4.7
77.5°	3.2
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)