

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247085

Luminaire Tested: **LD8B120D010 ER8B120950 8LBW0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P247085
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25264)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B120D010 ER8B120950 8LBW0LI
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 5000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12111.0 lumens
Efficiency: N/A
Efficacy: 102.4 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.22
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 118.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247085

CATALOG NUMBER: LD8B120D010 ER8B120950 8LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P247085

CATALOG NUMBER: LD8B120D010 ER8B120950 8LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	94	92
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75
4	93	84	78	73	91	83	77	72	81	75	71	79	74	70	77	73	70	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51
8	72	61	54	49	71	60	54	49	59	53	49	58	52	48	57	52	48	47
9	68	56	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43
10	64	53	46	41	63	52	46	41	51	45	41	50	45	41	50	45	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	208398
5°	212463
10°	221576
15°	234096
20°	242869
25°	244633
30°	233067
35°	205579
40°	165726
45°	117662
50°	70712
55°	31859
60°	8215
65°	1773
70°	875
75°	584
80°	284
85°	0



TEST NUMBER: P247085

CATALOG NUMBER: LD8B120D010 ER8B120950 8LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	662.1	5.5
10°-20°	2073.2	17.1
20°-30°	3278.6	27.1
30°-40°	3368.9	27.8
40°-50°	2089.8	17.3
50°-60°	592.5	4.9
60°-70°	40.0	0.3
70°-80°	5.4	0.0
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6013.9	49.7
0°-40°	9382.7	77.5
0°-60°	12064.9	99.6
0°-90°	12111.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12111.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6758	
5°	6864	662
15°	7333	2073
25°	7190	3279
35°	5461	3369
45°	2698	2090
55°	593	592
65°	24	40
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P247085

CATALOG NUMBER: LD8B120D010 ER8B120950 8LBW0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	6758.2
2.5°	6771.2
5°	6863.8
7.5°	6972.5
10°	7076.4
12.5°	7204.6
15°	7332.9
17.5°	7405.9
20°	7401.1
22.5°	7329.6
25°	7190.0
27.5°	6936.8
30°	6545.6
32.5°	6030.9
35°	5461.1
37.5°	4816.7
40°	4117.0
42.5°	3389.6
45°	2698.1
47.5°	2055.3
50°	1474.0
52.5°	992.0
55°	592.6
57.5°	305.2
60°	133.2
62.5°	53.6
65°	24.3
67.5°	14.6
70°	9.7
72.5°	6.5
75°	4.9
77.5°	3.3
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)