

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P248015

Luminaire Tested: **LD8B150D010 ER8B150930 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P248015
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-71)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B150D010 ER8B150930 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13086.5 lumens
Efficiency: N/A
Efficacy: 82.6 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 158.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P248015

CATALOG NUMBER: LD8B150D010 ER8B150930 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P248015

CATALOG NUMBER: LD8B150D010 ER8B150930 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74
4	93	84	77	72	91	82	76	72	80	75	71	78	74	70	76	72	69	67
5	87	77	70	65	85	76	70	65	74	68	64	72	67	64	71	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47
9	68	57	50	46	67	56	50	46	55	49	45	54	49	45	54	49	45	43
10	64	53	47	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P248015

CATALOG NUMBER: LD8B150D010 ER8B150930 8LBW0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	865.3	6.6
10°-20°	2436.9	18.6
20°-30°	3558.7	27.2
30°-40°	3200.5	24.5
40°-50°	1750.3	13.4
50°-60°	867.8	6.6
60°-70°	342.7	2.6
70°-80°	55.2	0.4
80°-90°	9.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6861.0	52.4
0°-40°	10061.5	76.9
0°-60°	12679.6	96.9
0°-90°	13086.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	13086.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9234	
5°	9137	865
15°	8634	2437
25°	7854	3559
35°	5166	3201
45°	2179	1750
55°	941	868
65°	343	343
75°	42	55
85°	12	9
90°	0	



TEST NUMBER: P248015

CATALOG NUMBER: LD8B150D010 ER8B150930 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	9234.5
2.5°	9208.8
5°	9137.0
7.5°	9043.7
10°	8912.4
12.5°	8772.8
15°	8634.1
17.5°	8485.4
20°	8316.9
22.5°	8124.6
25°	7853.6
27.5°	7397.8
30°	6789.1
32.5°	6022.0
35°	5165.6
37.5°	4310.8
40°	3494.0
42.5°	2758.2
45°	2179.3
47.5°	1746.6
50°	1441.9
52.5°	1173.5
55°	941.4
57.5°	760.6
60°	608.6
62.5°	481.5
65°	342.7
67.5°	204.0
70°	123.1
72.5°	69.4
75°	42.1
77.5°	27.2
80°	19.8
82.5°	6.6
85°	11.5
87.5°	4.9
90°	0.0

(END OF REPORT)