

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P249948

Luminaire Tested: **LD8B120D010 ER8B1209730 8LBM0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P249948
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13954)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B120D010 ER8B1209730 8LBM0H
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8831.1 lumens
Efficiency: N/A
Efficacy: 74.6 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 118.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P249948

CATALOG NUMBER: LD8B120D010 ER8B1209730 8LBM0H

Luminous Intensity Polar Plot





TEST NUMBER: P249948

CATALOG NUMBER: LD8B120D010 ER8B1209730 8LBM0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86
3	101	95	90	85	99	93	89	85	91	87	83	88	85	82	86	83	81	79
4	96	88	82	78	94	87	82	77	85	80	76	83	79	76	81	77	75	73
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	71	67	64	63
7	81	72	65	61	80	71	65	61	70	64	60	68	64	60	67	63	60	58
8	77	67	61	57	76	67	61	56	65	60	56	64	60	56	63	59	56	54
9	73	63	57	53	72	63	57	53	62	56	53	61	56	52	60	55	52	51
10	70	60	53	49	69	59	53	49	58	53	49	57	53	49	57	52	49	48

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P249948

CATALOG NUMBER: LD8B120D010 ER8B1209730 8LBM0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	842.7	9.5
10°-20°	2120.2	24.0
20°-30°	2752.4	31.2
30°-40°	2077.5	23.5
40°-50°	760.2	8.6
50°-60°	212.5	2.4
60°-70°	55.8	0.6
70°-80°	9.4	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5715.3	64.7
0°-40°	7792.7	88.2
0°-60°	8765.4	99.3
0°-90°	8831.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8831.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9243	
5°	9072	843
15°	7536	2120
25°	6084	2752
35°	3355	2077
45°	912	760
55°	218	212
65°	52	56
75°	8	9
85°	0	0
90°	0	



TEST NUMBER: P249948

CATALOG NUMBER: LD8B120D010 ER8B1209730 8LBM0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	9243.2
1°	9257.0
2°	9246.0
3°	9210.2
4°	9149.6
5°	9072.5
6°	8959.5
7°	8835.6
8°	8692.4
9°	8535.4
10°	8370.1
11°	8204.9
12°	8034.1
13°	7860.6
14°	7695.3
15°	7535.6
16°	7384.1
17°	7238.1
18°	7105.9
19°	6968.2
20°	6827.8
22.5°	6478.0
25°	6084.1
27.5°	5563.6
30°	4930.1
32.5°	4167.2
35°	3354.7
37.5°	2561.4
40°	1848.1
42.5°	1308.3
45°	911.7
47.5°	641.7
50°	432.4
52.5°	316.7
55°	217.6
57.5°	157.0
60°	104.7
62.5°	77.1
65°	52.3
67.5°	35.8
70°	19.3
72.5°	13.8
75°	8.3
77.5°	2.8
80°	2.8



TEST NUMBER: P249948

CATALOG NUMBER: LD8B120D010 ER8B1209730 8LBM0H

CANDELA DISTRIBUTION (continued):

	0°
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)