

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247093

Luminaire Tested: **LD8B120D010 ER8B1209730 8LBW0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P247093
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25264)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B120D010 ER8B1209730 8LBW0LI
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9674.9 lumens
Efficiency: N/A
Efficacy: 81.8 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.22
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 118.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247093

CATALOG NUMBER: LD8B120D010 ER8B1209730 8LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P247093

CATALOG NUMBER: LD8B120D010 ER8B1209730 8LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	94	92
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75
4	93	84	78	73	91	83	77	72	81	75	71	79	74	70	77	73	70	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51
8	72	61	54	49	71	60	54	49	59	53	49	58	52	48	57	52	48	47
9	68	56	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43
10	64	53	46	41	63	52	46	41	51	45	41	50	45	41	50	45	41	39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P247093

CATALOG NUMBER: LD8B120D010 ER8B1209730 8LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	528.9	5.5
10°-20°	1656.2	17.1
20°-30°	2619.1	27.1
30°-40°	2691.3	27.8
40°-50°	1669.4	17.3
50°-60°	473.3	4.9
60°-70°	32.0	0.3
70°-80°	4.3	0.0
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4804.2	49.7
0°-40°	7495.5	77.5
0°-60°	9638.2	99.6
0°-90°	9674.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9674.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5399	
5°	5483	529
15°	5858	1656
25°	5744	2619
35°	4363	2691
45°	2155	1669
55°	473	473
65°	19	32
75°	4	4
85°	0	1
90°	0	



TEST NUMBER: P247093

CATALOG NUMBER: LD8B120D010 ER8B1209730 8LBW0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	5398.9
2.5°	5409.2
5°	5483.2
7.5°	5570.1
10°	5653.0
12.5°	5755.5
15°	5858.0
17.5°	5916.3
20°	5912.5
22.5°	5855.3
25°	5743.8
27.5°	5541.5
30°	5229.0
32.5°	4817.9
35°	4362.7
37.5°	3847.9
40°	3288.9
42.5°	2707.8
45°	2155.4
47.5°	1641.9
50°	1177.5
52.5°	792.4
55°	473.4
57.5°	243.8
60°	106.4
62.5°	42.8
65°	19.4
67.5°	11.7
70°	7.7
72.5°	5.2
75°	3.9
77.5°	2.6
80°	1.3
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)