

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P248045

Luminaire Tested: **LD8B150D010 ER8B150950 8LBM0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P248045
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13941)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B150D010 ER8B150950 8LBM0WMH
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
90 CRI 5000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14161.9 lumens
Efficiency: N/A
Efficacy: 89.3 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.9
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 158.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P248045

CATALOG NUMBER: LD8B150D010 ER8B150950 8LBM0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P248045

CATALOG NUMBER: LD8B150D010 ER8B150950 8LBM0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74
5	92	83	77	73	90	82	76	72	80	75	72	79	74	71	77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	58	66	61	57	65	60	57	56
9	74	64	58	54	73	64	58	54	63	58	54	62	57	54	61	57	54	52
10	71	61	55	51	70	60	55	51	60	54	51	59	54	51	58	54	50	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	481709
5°	475508
10°	445767
15°	407639
20°	375269
25°	340054
30°	281581
35°	197485
40°	112385
45°	55118
50°	27201
55°	12333
60°	5871
65°	3159
70°	388
75°	512
80°	0
85°	0



TEST NUMBER: P248045

CATALOG NUMBER: LD8B150D010 ER8B150950 8LBM0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1429.5	10.1
10°-20°	3584.5	25.3
20°-30°	4524.9	32.0
30°-40°	3255.1	23.0
40°-50°	1077.3	7.6
50°-60°	234.6	1.7
60°-70°	48.4	0.3
70°-80°	5.1	0.0
80°-90°	2.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	9539.0	67.4
0°-40°	12794.1	90.3
0°-60°	14106.1	99.6
0°-90°	14161.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	14161.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15622	
5°	15362	###
15°	12769	3585
25°	9994	4525
35°	5246	3255
45°	1264	1077
55°	229	235
65°	43	48
75°	4	5
85°	0	2
90°	0	



TEST NUMBER: P248045

CATALOG NUMBER: LD8B150D010 ER8B150950 8LBM0WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	15621.5
1°	15643.1
2°	15625.7
3°	15573.8
4°	15478.6
5°	15361.7
6°	15201.5
7°	14993.8
8°	14764.3
9°	14513.3
10°	14236.3
11°	13955.0
12°	13647.6
13°	13353.3
14°	13054.6
15°	12769.0
16°	12487.6
17°	12219.2
18°	11950.9
19°	11695.5
20°	11435.8
21°	11171.8
22°	10912.1
23°	10630.7
24°	10327.8
25°	9994.5
26°	9643.8
27°	9254.2
28°	8843.1
29°	8384.2
30°	7908.1
31°	7406.0
32°	6877.9
33°	6323.9
34°	5782.8
35°	5246.1
37.5°	3938.9
40°	2791.9
42.5°	1891.6
45°	1263.9
47.5°	848.3
50°	567.0
52.5°	342.0
55°	229.4
57.5°	160.1



TEST NUMBER: P248045

CATALOG NUMBER: LD8B150D010 ER8B150950 8LBM0WMH

CANDELA DISTRIBUTION (continued):

	0°
60°	95.2
62.5°	64.9
65°	43.3
67.5°	39.0
70°	4.3
72.5°	8.7
75°	4.3
77.5°	4.3
80°	0.0
82.5°	8.7
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)