

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243943

Luminaire Tested: **LD8B15D010 ER8B15827 8LBMOLI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P243943  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-11)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B15D010 ER8B15827 8LBM0LI  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 2700 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1493.0 lumens  
Efficiency: N/A  
Efficacy: 103.7 lumens/watt  
Spacing Criteria (0/90/45): 0.63 / 0.63 / 0.72  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P243943

CATALOG NUMBER: LD8B15D010 ER8B15827 8LBM0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P243943

CATALOG NUMBER: LD8B15D010 ER8B15827 8LBM0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	73	80	75	72		79	75	72		77	74	71	70
7	86	78	72	69	85	77	72	68	76	71	68		75	71	68		74	70	67	66
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70	67	64	62
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67	63	60	59
10	76	67	62	58	75	67	61	58	66	61	58		65	61	58		64	60	58	56

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	80313
5°	76862
10°	68426
15°	54970
20°	43054
25°	34762
30°	26936
35°	15344
40°	5789
45°	2494
50°	1003
55°	376
60°	204
65°	139
70°	81
75°	60
80°	0
85°	0



TEST NUMBER: P243943

CATALOG NUMBER: LD8B15D010 ER8B15827 8LBM0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	227.9	15.3
10°-20°	478.1	32.0
20°-30°	467.9	31.3
30°-40°	258.9	17.3
40°-50°	50.1	3.4
50°-60°	7.7	0.5
60°-70°	1.9	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1173.9	78.6
0°-40°	1432.8	96.0
0°-60°	1490.6	99.8
0°-90°	1493.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1493.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2604	
5°	2483	228
15°	1722	478
25°	1022	468
35°	408	259
45°	57	50
55°	7	8
65°	2	2
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P243943

CATALOG NUMBER: LD8B15D010 ER8B15827 8LBM0LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2604.5
2.5°	2568.7
5°	2483.1
7.5°	2363.0
10°	2185.3
12.5°	1960.6
15°	1721.9
17.5°	1498.1
20°	1312.0
22.5°	1158.0
25°	1021.7
27.5°	893.3
30°	756.5
32.5°	596.0
35°	407.6
37.5°	245.2
40°	143.8
42.5°	89.8
45°	57.2
47.5°	35.8
50°	20.9
52.5°	11.6
55°	7.0
57.5°	4.2
60°	3.3
62.5°	2.3
65°	1.9
67.5°	1.4
70°	0.9
72.5°	0.5
75°	0.5
77.5°	0.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)