

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250362

Luminaire Tested: **LD8B150D010 ER8B1509727 8LBN0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250362
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B150D010 ER8B1509727 8LBN0GPH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8858.0 lumens
Efficiency: N/A
Efficacy: 55.9 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 158.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250362

CATALOG NUMBER: LD8B150D010 ER8B1509727 8LBN0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P250362

CATALOG NUMBER: LD8B150D010 ER8B1509727 8LBN0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72	79	75	71	77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250362

CATALOG NUMBER: LD8B150D010 ER8B1509727 8LBN0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1270.6	14.3
10°-20°	2761.6	31.2
20°-30°	2964.8	33.5
30°-40°	1602.4	18.1
40°-50°	250.0	2.8
50°-60°	6.8	0.1
60°-70°	1.7	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6997.1	79.0
0°-40°	8599.5	97.1
0°-60°	8856.3	100.0
0°-90°	8858.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8858.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14154	
5°	13875	###
15°	9860	2762
25°	6572	2965
35°	2517	1602
45°	231	250
55°	0	7
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250362

CATALOG NUMBER: LD8B150D010 ER8B1509727 8LBN0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	14154.2
1°	14181.1
2°	14167.8
3°	14119.2
4°	14026.0
5°	13875.0
6°	13667.2
7°	13387.6
8°	13037.6
9°	12634.7
10°	12186.8
11°	11716.9
12°	11229.4
13°	10742.4
14°	10290.0
15°	9860.3
16°	9465.8
17°	9084.6
18°	8730.1
19°	8398.1
20°	8078.8
21°	7768.5
22°	7475.8
23°	7183.7
24°	6877.9
25°	6571.9
26°	6261.6
27°	5907.3
28°	5517.1
29°	5118.8
30°	4702.0
31°	4254.5
32°	3806.5
33°	3363.5
34°	2916.0
35°	2517.0
37.5°	1608.6
40°	930.7
42.5°	496.5
45°	230.6
47.5°	124.3
50°	40.2
52.5°	4.5
55°	0.0
57.5°	4.5



TEST NUMBER: P250362

CATALOG NUMBER: LD8B150D010 ER8B1509727 8LBN0GPH

CANDELA DISTRIBUTION (continued):

	0°
60°	4.5
62.5°	0.0
65°	0.0
67.5°	4.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)