

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250033

Luminaire Tested: **LD8B150D010 ER8B1509730 8LBN0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250033  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13951)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B150D010 ER8B1509730 8LBN0WMH  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 3000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10227.0 lumens  
Efficiency: N/A  
Efficacy: 64.5 lumens/watt  
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.79  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 158.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250033

CATALOG NUMBER: LD8B150D010 ER8B1509730 8LBN0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P250033

CATALOG NUMBER: LD8B150D010 ER8B1509730 8LBN0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88
3	103	97	92	89	101	96	91	88	93	89	86	91	88	85	89	86	84	82
4	98	91	86	82	97	90	85	81	88	84	80	86	82	79	84	81	79	77
5	94	86	80	76	92	85	80	76	83	78	75	81	77	74	80	76	74	72
6	89	81	75	71	88	80	75	71	79	74	70	77	73	70	76	72	69	68
7	85	76	71	67	84	76	70	66	74	70	66	73	69	66	72	68	65	64
8	81	72	66	63	80	72	66	62	71	66	62	70	65	62	69	65	62	60
9	78	68	63	59	77	68	63	59	67	62	59	66	62	58	65	61	58	57
10	74	65	59	56	73	65	59	56	64	59	56	63	59	55	62	58	55	54

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P250033

CATALOG NUMBER: LD8B150D010 ER8B1509730 8LBN0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1352.0	13.2
10°-20°	3101.9	30.3
20°-30°	3295.5	32.2
30°-40°	1880.2	18.4
40°-50°	466.2	4.6
50°-60°	91.7	0.9
60°-70°	27.7	0.3
70°-80°	6.6	0.1
80°-90°	5.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7749.4	75.8
0°-40°	9629.6	94.2
0°-60°	10187.5	99.6
0°-90°	10227.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10227.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	14896	
5°	14632	###
15°	11144	3102
25°	7275	3295
35°	2940	1880
45°	527	466
55°	85	92
65°	21	28
75°	0	7
85°	7	5
90°	0	



TEST NUMBER: P250033

CATALOG NUMBER: LD8B150D010 ER8B1509730 8LBN0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	14895.9
1°	14924.4
2°	14913.7
3°	14860.3
4°	14767.8
5°	14632.5
6°	14454.6
7°	14208.9
8°	13927.7
9°	13596.8
10°	13233.6
11°	12849.4
12°	12436.4
13°	12016.4
14°	11585.7
15°	11144.3
16°	10727.9
17°	10307.9
18°	9912.8
19°	9510.6
20°	9129.8
22.5°	8186.5
25°	7275.3
27.5°	6296.6
30°	5214.5
32.5°	4054.0
35°	2940.0
37.5°	2025.2
40°	1309.9
42.5°	829.4
45°	526.8
47.5°	345.3
50°	217.1
52.5°	131.8
55°	85.4
57.5°	67.7
60°	42.7
62.5°	39.1
65°	21.4
67.5°	21.4
70°	17.9
72.5°	10.7
75°	0.0
77.5°	3.6
80°	3.6



TEST NUMBER: P250033

CATALOG NUMBER: LD8B150D010 ER8B1509730 8LBN0WMH

**CANDELA DISTRIBUTION (continued):**

	0°
82.5°	7.1
85°	7.1
87.5°	3.6
90°	0.0

(END OF REPORT)