

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244885

Luminaire Tested: **LD8B15D010 ER8B15830 8LBS0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244885
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-14)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B15D010 ER8B15830 8LBS0WMH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1579.0 lumens
Efficiency: N/A
Efficacy: 109.7 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244885

CATALOG NUMBER: LD8B15D010 ER8B15830 8LBS0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244885

CATALOG NUMBER: LD8B15D010 ER8B15830 8LBS0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95	94	92	91
2	105	99	94	89	102	97	92	88	94	90	86		90	87	85		88	85	83	81
3	98	90	83	78	95	88	82	78	85	80	76		83	79	75		80	77	74	72
4	91	82	75	69	89	80	74	69	78	72	68		76	71	67		74	70	66	65
5	85	74	67	62	83	73	67	61	71	65	61		70	64	60		68	63	60	58
6	79	68	61	55	77	67	60	55	66	59	55		64	58	54		63	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49		59	53	49		58	53	49	47
8	69	58	50	45	68	57	50	45	56	49	45		55	49	45		54	48	45	43
9	65	53	46	41	64	53	46	41	52	45	41		51	45	41		50	45	41	39
10	61	50	43	38	60	49	42	38	48	42	38		47	42	38		46	41	37	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	27608
5°	27521
10°	27273
15°	27005
20°	26715
25°	26290
30°	25569
35°	24405
40°	22619
45°	19096
50°	13101
55°	7226
60°	3633
65°	2043
70°	1109
75°	786
80°	497
85°	318



TEST NUMBER: P244885

CATALOG NUMBER: LD8B15D010 ER8B15830 8LBS0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.3	5.3
10°-20°	238.6	15.1
20°-30°	355.2	22.5
30°-40°	403.5	25.6
40°-50°	329.8	20.9
50°-60°	129.2	8.2
60°-70°	30.1	1.9
70°-80°	7.2	0.5
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	678.0	42.9
0°-40°	1081.5	68.5
0°-60°	1540.5	97.6
0°-90°	1579.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1579.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	895	
5°	889	84
15°	846	239
25°	773	355
35°	648	403
45°	438	330
55°	134	129
65°	28	30
75°	7	7
85°	1	1
90°	0	



TEST NUMBER: P244885

CATALOG NUMBER: LD8B15D010 ER8B15830 8LBS0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	895.3
2.5°	893.8
5°	889.1
7.5°	881.0
10°	871.0
12.5°	858.7
15°	845.9
17.5°	830.7
20°	814.1
22.5°	794.6
25°	772.7
27.5°	747.1
30°	718.1
32.5°	685.3
35°	648.3
37.5°	607.5
40°	561.9
42.5°	506.8
45°	437.9
47.5°	357.2
50°	273.1
52.5°	196.2
55°	134.4
57.5°	87.9
60°	58.9
62.5°	40.4
65°	28.0
67.5°	18.5
70°	12.3
72.5°	8.5
75°	6.6
77.5°	4.7
80°	2.8
82.5°	1.4
85°	0.9
87.5°	0.5
90°	0.0

(END OF REPORT)