

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245533

Luminaire Tested: **LD8B15D010 ER8B15830 8LBW0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245533
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-46)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B15D010 ER8B15830 8LBW0GPH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1325.0 lumens
Efficiency: N/A
Efficacy: 92.0 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245533

CATALOG NUMBER: LD8B15D010 ER8B15830 8LBW0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245533

CATALOG NUMBER: LD8B15D010 ER8B15830 8LBW0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100		100	98	97		96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89		93	90	87		90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84	81	78	76
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78	74	71	70
5	88	79	72	67	87	78	72	67	76	71	66		74	70	66		73	69	65	64
6	83	73	66	61	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		65	59	56		63	59	55	54
8	74	63	56	52	73	63	56	52	61	56	51		60	55	51		59	55	51	49
9	70	59	52	48	69	58	52	48	57	52	48		57	51	47		56	51	47	46
10	66	55	49	44	65	55	49	44	54	48	44		53	48	44		52	47	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	31814
5°	31062
10°	30088
15°	29654
20°	29304
25°	28676
30°	26858
35°	21932
40°	13095
45°	7863
50°	5666
55°	3855
60°	2418
65°	1189
70°	298
75°	119
80°	89
85°	0



TEST NUMBER: P245533

CATALOG NUMBER: LD8B15D010 ER8B15830 8LBW0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.4	7.1
10°-20°	262.1	19.8
20°-30°	384.9	29.1
30°-40°	349.0	26.3
40°-50°	149.4	11.3
50°-60°	66.1	5.0
60°-70°	17.6	1.3
70°-80°	1.4	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	741.5	56.0
0°-40°	1090.4	82.3
0°-60°	1305.9	98.6
0°-90°	1325.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1325.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1032	
5°	1004	94
15°	929	262
25°	843	385
35°	583	349
45°	180	149
55°	72	66
65°	16	18
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P245533

CATALOG NUMBER: LD8B15D010 ER8B15830 8LBW0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1031.7
2.5°	1023.6
5°	1003.5
7.5°	980.5
10°	960.9
12.5°	944.7
15°	928.9
17.5°	912.1
20°	893.0
22.5°	870.5
25°	842.8
27.5°	805.5
30°	754.3
32.5°	682.5
35°	582.6
37.5°	451.5
40°	325.3
42.5°	234.8
45°	180.3
47.5°	145.4
50°	118.1
52.5°	93.7
55°	71.7
57.5°	53.6
60°	39.2
62.5°	27.3
65°	16.3
67.5°	7.2
70°	3.3
72.5°	1.9
75°	1.0
77.5°	0.5
80°	0.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)