

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P249971

Luminaire Tested: **LD8B175D010 ER8B175835 8LBN0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P249971
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13951)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B175D010 ER8B175835 8LBN0WMH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3500 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15674.0 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.79
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 177.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P249971

CATALOG NUMBER: LD8B175D010 ER8B175835 8LBN0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P249971

CATALOG NUMBER: LD8B175D010 ER8B175835 8LBN0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88
3	103	97	92	89	101	96	91	88	93	89	86	91	88	85	89	86	84	82
4	98	91	86	82	97	90	85	81	88	84	80	86	82	79	84	81	79	77
5	94	86	80	76	92	85	80	76	83	78	75	81	77	74	80	76	74	72
6	89	81	75	71	88	80	75	71	79	74	70	77	73	70	76	72	69	68
7	85	76	71	67	84	76	70	66	74	70	66	73	69	66	72	68	65	64
8	81	72	66	63	80	72	66	62	71	66	62	70	65	62	69	65	62	60
9	78	68	63	59	77	68	63	59	67	62	59	66	62	58	65	61	58	57
10	74	65	59	56	73	65	59	56	64	59	56	63	59	55	62	58	55	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	703978
5°	694174
10°	635070
15°	545260
20°	459165
25°	379372
30°	284562
35°	169621
40°	80814
45°	35206
50°	15965
55°	7032
60°	4033
65°	2393
70°	2470
75°	0
80°	977
85°	3856



TEST NUMBER: P249971

CATALOG NUMBER: LD8B175D010 ER8B175835 8LBN0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2072.1	13.2
10°-20°	4754.1	30.3
20°-30°	5050.6	32.2
30°-40°	2881.6	18.4
40°-50°	714.5	4.6
50°-60°	140.5	0.9
60°-70°	42.4	0.3
70°-80°	10.1	0.1
80°-90°	8.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	11876.7	75.8
0°-40°	14758.4	94.2
0°-60°	15613.4	99.6
0°-90°	15674.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	15674.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	22830	
5°	22426	###
15°	17080	4754
25°	11150	5051
35°	4506	2882
45°	807	715
55°	131	140
65°	33	42
75°	0	10
85°	11	8
90°	0	



TEST NUMBER: P249971

CATALOG NUMBER: LD8B175D010 ER8B175835 8LBN0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	22829.5
1°	22873.3
2°	22856.9
3°	22775.1
4°	22633.3
5°	22425.9
6°	22153.3
7°	21776.7
8°	21345.7
9°	20838.6
10°	20282.0
11°	19693.1
12°	19060.1
13°	18416.4
14°	17756.4
15°	17079.9
16°	16441.7
17°	15798.0
18°	15192.4
19°	14576.1
20°	13992.4
22.5°	12546.6
25°	11150.1
27.5°	9650.2
30°	7991.8
32.5°	6213.3
35°	4505.9
37.5°	3103.9
40°	2007.6
42.5°	1271.2
45°	807.3
47.5°	529.3
50°	332.8
52.5°	202.0
55°	130.8
57.5°	103.7
60°	65.4
62.5°	59.9
65°	32.8
67.5°	32.8
70°	27.4
72.5°	16.4
75°	0.0
77.5°	5.5
80°	5.5



TEST NUMBER: P249971

CATALOG NUMBER: LD8B175D010 ER8B175835 8LBN0WMH

CANDELA DISTRIBUTION (continued):

	0°
82.5°	10.9
85°	10.9
87.5°	5.5
90°	0.0

(END OF REPORT)