

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P248004

Luminaire Tested: **LD8B175D010 ER8B175935 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P248004
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-71)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B175D010 ER8B175935 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 3500 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15258.0 lumens
Efficiency: N/A
Efficacy: 86.1 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 177.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P248004

CATALOG NUMBER: LD8B175D010 ER8B175935 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P248004

CATALOG NUMBER: LD8B175D010 ER8B175935 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74
4	93	84	77	72	91	82	76	72	80	75	71	78	74	70	76	72	69	67
5	87	77	70	65	85	76	70	65	74	68	64	72	67	64	71	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47
9	68	57	50	46	67	56	50	46	55	49	45	54	49	45	54	49	45	43
10	64	53	47	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	332005
5°	329757
10°	325369
15°	321370
20°	318210
25°	311552
30°	281852
35°	226720
40°	163991
45°	110811
50°	80652
55°	59014
60°	43763
65°	29157
70°	12938
75°	5850
80°	4102
85°	4776



TEST NUMBER: P248004

CATALOG NUMBER: LD8B175D010 ER8B175935 8LBW0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1008.9	6.6
10°-20°	2841.3	18.6
20°-30°	4149.2	27.2
30°-40°	3731.6	24.5
40°-50°	2040.8	13.4
50°-60°	1011.8	6.6
60°-70°	399.5	2.6
70°-80°	64.4	0.4
80°-90°	10.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7999.4	52.4
0°-40°	11731.0	76.9
0°-60°	14783.6	96.9
0°-90°	15258.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	15258.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10767	
5°	10653	###
15°	10067	2841
25°	9157	4149
35°	6023	3732
45°	2541	2041
55°	1098	1012
65°	400	400
75°	49	64
85°	14	10
90°	0	



TEST NUMBER: P248004

CATALOG NUMBER: LD8B175D010 ER8B175935 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	10766.7
2.5°	10736.9
5°	10653.1
7.5°	10544.3
10°	10391.2
12.5°	10228.5
15°	10066.7
17.5°	9893.4
20°	9697.0
22.5°	9472.6
25°	9156.8
27.5°	8625.3
30°	7915.7
32.5°	7021.2
35°	6022.7
37.5°	5026.1
40°	4073.9
42.5°	3216.0
45°	2541.0
47.5°	2036.5
50°	1681.2
52.5°	1368.2
55°	1097.7
57.5°	886.8
60°	709.6
62.5°	561.3
65°	399.6
67.5°	237.8
70°	143.5
72.5°	80.9
75°	49.1
77.5°	31.8
80°	23.1
82.5°	7.7
85°	13.5
87.5°	5.8
90°	0.0

(END OF REPORT)