

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245323

Luminaire Tested: **LD8B15D010 ER8B15835 8LBS0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245323
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B15D010 ER8B15835 8LBS0WH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3500 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1642.0 lumens
Efficiency: N/A
Efficacy: 114.0 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245323

CATALOG NUMBER: LD8B15D010 ER8B15835 8LBS0WH

Luminous Intensity Polar Plot





TEST NUMBER: P245323

CATALOG NUMBER: LD8B15D010 ER8B15835 8LBS0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60
6	80	70	63	57	79	69	62	57	67	61	57	66	60	56	64	60	56	54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	28678
5°	28787
10°	29151
15°	29721
20°	30144
25°	30271
30°	29343
35°	26780
40°	23166
45°	18237
50°	11763
55°	5774
60°	2374
65°	1043
70°	298
75°	119
80°	89
85°	0



TEST NUMBER: P245323

CATALOG NUMBER: LD8B15D010 ER8B15835 8LBS0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.8	5.4
10°-20°	263.1	16.0
20°-30°	407.4	24.8
30°-40°	441.3	26.9
40°-50°	317.6	19.3
50°-60°	106.2	6.5
60°-70°	16.1	1.0
70°-80°	1.4	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	759.3	46.2
0°-40°	1200.6	73.1
0°-60°	1624.4	98.9
0°-90°	1642.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1642.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	930	
5°	930	89
15°	931	263
25°	890	407
35°	711	441
45°	418	318
55°	107	106
65°	14	16
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P245323

CATALOG NUMBER: LD8B15D010 ER8B15835 8LBS0WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	930.0
2.5°	930.0
5°	930.0
7.5°	930.5
10°	931.0
12.5°	932.0
15°	931.0
17.5°	927.2
20°	918.6
22.5°	905.8
25°	889.7
27.5°	864.0
30°	824.1
32.5°	771.8
35°	711.4
37.5°	646.3
40°	575.5
42.5°	499.5
45°	418.2
47.5°	330.3
50°	245.2
52.5°	168.2
55°	107.4
57.5°	64.2
60°	38.5
62.5°	23.3
65°	14.3
67.5°	7.1
70°	3.3
72.5°	1.4
75°	1.0
77.5°	1.0
80°	0.5
82.5°	0.5
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)