

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250531

Luminaire Tested: **LD8B175D010 ER8B1759727 8LBM0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250531
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14005)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B175D010 ER8B1759727 8LBM0GPH
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11063.0 lumens
Efficiency: N/A
Efficacy: 62.4 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 177.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250531

CATALOG NUMBER: LD8B175D010 ER8B1759727 8LBM0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P250531

CATALOG NUMBER: LD8B175D010 ER8B1759727 8LBM0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72	71
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	82	74	68	64	73	68	64		72	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	59	58
9	76	66	61	57	75	66	60	57	65	60	56		64	59	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250531

CATALOG NUMBER: LD8B175D010 ER8B1759727 8LBM0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1249.1	11.3
10°-20°	2970.0	26.8
20°-30°	3700.1	33.4
30°-40°	2495.8	22.6
40°-50°	590.2	5.3
50°-60°	43.1	0.4
60°-70°	7.7	0.1
70°-80°	5.7	0.1
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7919.2	71.6
0°-40°	10415.0	94.1
0°-60°	11048.3	99.9
0°-90°	11063.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11063.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14031	
5°	13624	###
15°	10547	2970
25°	8202	3700
35°	4001	2496
45°	641	590
55°	19	43
65°	0	8
75°	14	6
85°	5	1
90°	0	



TEST NUMBER: P250531

CATALOG NUMBER: LD8B175D010 ER8B1759727 8LBM0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	14030.8
2.5°	14006.9
5°	13624.0
7.5°	12930.1
10°	12073.6
12.5°	11264.9
15°	10547.1
17.5°	9929.7
20°	9360.3
22.5°	8814.7
25°	8202.2
27.5°	7403.1
30°	6426.8
32.5°	5244.9
35°	4000.6
37.5°	2861.7
40°	1866.3
42.5°	1115.1
45°	641.2
47.5°	358.9
50°	177.0
52.5°	81.4
55°	19.1
57.5°	4.8
60°	9.6
62.5°	14.4
65°	0.0
67.5°	9.6
70°	4.8
72.5°	4.8
75°	14.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	4.8
87.5°	0.0
90°	0.0

(END OF REPORT)