

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246625

Luminaire Tested: **LD8B15D010 ER8B15840 8LBN0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246625
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201839)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B15D010 ER8B15840 8LBN0MW
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 4000 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1435.0 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.85
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246625

CATALOG NUMBER: LD8B15D010 ER8B15840 8LBN0MW

Luminous Intensity Polar Plot





TEST NUMBER: P246625

CATALOG NUMBER: LD8B15D010 ER8B15840 8LBN0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	109	106	104	101	102	100	98	98	97	95	95	94	92	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67
5	87	78	71	66	85	77	70	65	75	69	65	73	68	64	71	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60	68	63	59	67	62	59	57
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	46406
5°	46072
10°	41983
15°	35988
20°	31893
25°	28461
30°	22984
35°	15946
40°	10120
45°	7518
50°	6414
55°	5623
60°	5032
65°	4495
70°	3877
75°	3562
80°	3321
85°	2937



TEST NUMBER: P246625

CATALOG NUMBER: LD8B15D010 ER8B15840 8LBN0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.3	9.6
10°-20°	317.5	22.1
20°-30°	377.6	26.3
30°-40°	266.9	18.6
40°-50°	137.8	9.6
50°-60°	94.5	6.6
60°-70°	61.3	4.3
70°-80°	32.2	2.2
80°-90°	9.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	832.4	58.0
0°-40°	1099.4	76.6
0°-60°	1331.6	92.8
0°-90°	1435.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1435.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1505	
5°	1488	137
15°	1127	318
25°	836	378
35°	424	267
45°	172	138
55°	105	94
65°	62	61
75°	30	32
85°	8	9
90°	0	1
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P246625

CATALOG NUMBER: LD8B15D010 ER8B15840 8LBN0MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1504.9
2.5°	1504.9
5°	1488.4
7.5°	1433.7
10°	1340.8
12.5°	1230.1
15°	1127.3
17.5°	1042.6
20°	971.9
22.5°	905.0
25°	836.5
27.5°	750.4
30°	645.5
32.5°	532.6
35°	423.6
37.5°	326.4
40°	251.4
42.5°	202.3
45°	172.4
47.5°	150.6
50°	133.7
52.5°	118.9
55°	104.6
57.5°	92.0
60°	81.6
62.5°	70.7
65°	61.6
67.5°	53.4
70°	43.0
72.5°	36.9
75°	29.9
77.5°	24.3
80°	18.7
82.5°	13.9
85°	8.3
87.5°	4.8
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P246625

CATALOG NUMBER: LD8B15D010 ER8B15840 8LBN0MW

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)