

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245761

Luminaire Tested: **LD8B15D010 ER8B15840 8LBS0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P245761  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-16)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B15D010 ER8B15840 8LBS0GPH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 4000 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1515.1 lumens  
Efficiency: N/A  
Efficacy: 105.2 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P245761

CATALOG NUMBER: LD8B15D010 ER8B15840 8LBS0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P245761

CATALOG NUMBER: LD8B15D010 ER8B15840 8LBS0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58
6	79	69	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53
7	74	63	56	50	73	62	55	50	61	55	50	59	54	50	58	53	49	48
8	70	58	51	46	68	57	50	46	56	50	45	55	49	45	54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	41	51	45	41	50	45	41	40
10	62	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	26815
5°	26735
10°	26471
15°	26200
20°	25924
25°	25501
30°	24804
35°	23671
40°	22011
45°	18586
50°	12617
55°	6591
60°	2960
65°	1445
70°	577
75°	357
80°	266
85°	177



TEST NUMBER: P245761

CATALOG NUMBER: LD8B15D010 ER8B15840 8LBS0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	81.9	5.4
10°-20°	231.5	15.3
20°-30°	344.6	22.7
30°-40°	391.7	25.9
40°-50°	320.3	21.1
50°-60°	119.4	7.9
60°-70°	21.9	1.4
70°-80°	3.4	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	657.9	43.4
0°-40°	1049.6	69.3
0°-60°	1489.3	98.3
0°-90°	1515.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1515.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	870	
5°	864	82
15°	821	231
25°	750	345
35°	629	392
45°	426	320
55°	123	119
65°	20	22
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P245761

CATALOG NUMBER: LD8B15D010 ER8B15840 8LBS0GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	869.6
2.5°	868.1
5°	863.7
7.5°	855.8
10°	845.4
12.5°	833.5
15°	820.7
17.5°	805.8
20°	790.0
22.5°	771.2
25°	749.5
27.5°	724.8
30°	696.6
32.5°	664.4
35°	628.8
37.5°	590.8
40°	546.8
42.5°	492.4
45°	426.2
47.5°	346.6
50°	263.0
52.5°	185.4
55°	122.6
57.5°	77.1
60°	48.0
62.5°	30.7
65°	19.8
67.5°	11.4
70°	6.4
72.5°	4.0
75°	3.0
77.5°	2.0
80°	1.5
82.5°	0.5
85°	0.5
87.5°	0.0
90°	0.0

(END OF REPORT)