

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244681

Luminaire Tested: **LD8B15D010 ER8B15840 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244681
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B15D010 ER8B15840 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 4000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1483.0 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244681

CATALOG NUMBER: LD8B15D010 ER8B15840 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244681

CATALOG NUMBER: LD8B15D010 ER8B15840 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	33140
5°	32474
10°	31447
15°	31021
20°	30837
25°	30448
30°	28809
35°	23761
40°	14838
45°	9542
50°	7397
55°	5693
60°	4317
65°	2802
70°	1199
75°	584
80°	266
85°	177



TEST NUMBER: P244681

CATALOG NUMBER: LD8B15D010 ER8B15840 8LBW0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.7	6.7
10°-20°	274.5	18.5
20°-30°	408.9	27.6
30°-40°	379.7	25.6
40°-50°	179.4	12.1
50°-60°	96.3	6.5
60°-70°	38.7	2.6
70°-80°	6.1	0.4
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	782.1	52.7
0°-40°	1161.9	78.3
0°-60°	1437.6	96.9
0°-90°	1483.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1483.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1075	
5°	1049	99
15°	972	275
25°	895	409
35°	631	380
45°	219	179
55°	106	96
65°	38	39
75°	5	6
85°	0	1
90°	0	



TEST NUMBER: P244681

CATALOG NUMBER: LD8B15D010 ER8B15840 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1074.7
2.5°	1067.3
5°	1049.1
7.5°	1026.0
10°	1004.3
12.5°	986.5
15°	971.7
17.5°	956.5
20°	939.7
22.5°	920.5
25°	894.9
27.5°	858.9
30°	809.1
32.5°	736.2
35°	631.2
37.5°	497.2
40°	368.6
42.5°	274.5
45°	218.8
47.5°	182.8
50°	154.2
52.5°	128.6
55°	105.9
57.5°	86.2
60°	70.0
62.5°	54.7
65°	38.4
67.5°	22.7
70°	13.3
72.5°	7.9
75°	4.9
77.5°	3.0
80°	1.5
82.5°	1.0
85°	0.5
87.5°	0.0
90°	0.0

(END OF REPORT)