

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244664

Luminaire Tested: **LD8B20D010 ER8B20827 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244664
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B20D010 ER8B20827 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 2700 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1989.0 lumens
Efficiency: N/A
Efficacy: 93.4 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244664

CATALOG NUMBER: LD8B20D010 ER8B20827 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244664

CATALOG NUMBER: LD8B20D010 ER8B20827 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	44447
5°	43556
10°	42174
15°	41607
20°	41360
25°	40836
30°	38640
35°	31870
40°	19902
45°	12795
50°	9926
55°	7640
60°	5785
65°	3765
70°	1605
75°	786
80°	355
85°	248



TEST NUMBER: P244664

CATALOG NUMBER: LD8B20D010 ER8B20827 8LBW0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.3	6.7
10°-20°	368.2	18.5
20°-30°	548.4	27.6
30°-40°	509.3	25.6
40°-50°	240.6	12.1
50°-60°	129.3	6.5
60°-70°	51.9	2.6
70°-80°	8.2	0.4
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1049.0	52.7
0°-40°	1558.3	78.3
0°-60°	1928.2	96.9
0°-90°	1989.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1989.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1441	
5°	1407	132
15°	1303	368
25°	1200	548
35°	847	509
45°	293	241
55°	142	129
65°	52	52
75°	7	8
85°	1	1
90°	0	



TEST NUMBER: P244664

CATALOG NUMBER: LD8B20D010 ER8B20827 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1441.4
2.5°	1431.5
5°	1407.1
7.5°	1376.0
10°	1346.9
12.5°	1323.1
15°	1303.3
17.5°	1282.8
20°	1260.4
22.5°	1234.6
25°	1200.2
27.5°	1152.0
30°	1085.2
32.5°	987.4
35°	846.6
37.5°	666.9
40°	494.4
42.5°	368.1
45°	293.4
47.5°	245.2
50°	206.9
52.5°	172.5
55°	142.1
57.5°	115.7
60°	93.8
62.5°	73.4
65°	51.6
67.5°	30.4
70°	17.8
72.5°	10.6
75°	6.6
77.5°	4.0
80°	2.0
82.5°	1.3
85°	0.7
87.5°	0.0
90°	0.0

(END OF REPORT)