

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244363

Luminaire Tested: **LD8B15D010 ER8B15927 8LBN0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244363
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27944)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B15D010 ER8B15927 8LBN0H
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1109.2 lumens
Efficiency: N/A
Efficacy: 77.0 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.79
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244363

CATALOG NUMBER: LD8B15D010 ER8B15927 8LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P244363

CATALOG NUMBER: LD8B15D010 ER8B15927 8LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	86	83	82
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	69	67
7	85	76	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	58		64	60	57	56
10	74	64	59	55	73	64	58	55	63	58	55		62	58	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244363

CATALOG NUMBER: LD8B15D010 ER8B15927 8LBN0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.4	12.8
10°-20°	318.2	28.7
20°-30°	361.8	32.6
30°-40°	212.5	19.2
40°-50°	57.0	5.1
50°-60°	13.5	1.2
60°-70°	3.1	0.3
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<hr/>		
0°-30°	822.4	74.1
0°-40°	1034.9	93.3
0°-60°	1105.4	99.7
0°-90°	1109.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1109.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1693	
5°	1573	142
15°	1138	318
25°	798	362
35°	331	212
45°	68	57
55°	14	14
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P244363

CATALOG NUMBER: LD8B15D010 ER8B15927 8LBN0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1693.2
1°	1683.9
2°	1666.7
3°	1642.4
4°	1610.9
5°	1573.4
6°	1531.1
7°	1483.1
8°	1435.2
9°	1386.8
10°	1340.8
11°	1295.8
12°	1253.5
13°	1214.1
14°	1174.8
15°	1138.0
16°	1102.2
17°	1066.5
18°	1032.1
19°	997.2
20°	963.1
21°	929.0
22°	896.5
23°	864.2
24°	831.3
25°	798.3
26°	764.2
27°	727.1
28°	688.2
29°	645.5
30°	599.4
32.5°	470.1
35°	330.8
37.5°	218.0
40°	142.8
42.5°	98.6
45°	68.2
47.5°	46.8
50°	31.0
52.5°	20.2
55°	13.5
57.5°	9.0
60°	6.0
62.5°	4.2
65°	3.0



TEST NUMBER: P244363

CATALOG NUMBER: LD8B15D010 ER8B15927 8LBN0H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.9
70°	1.1
72.5°	0.8
75°	0.8
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)