

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243931

Luminaire Tested: **LD8B15D010 ER8B15927 8LBNOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P243931
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-10)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B15D010 ER8B15927 8LBN0LI
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1175.6 lumens
Efficiency: N/A
Efficacy: 81.6 lumens/watt
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.32
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P243931

CATALOG NUMBER: LD8B15D010 ER8B15927 8LBN0LI

Luminous Intensity Polar Plot






TEST NUMBER: P243931

CATALOG NUMBER: LD8B15D010 ER8B15927 8LBN0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	100	108	104	101	99	101	99	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	91		94	92	89		92	90	88	87
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		89	86	84	83
5	98	91	86	83	96	90	86	82	88	85	82		87	84	81		85	83	80	79
6	94	87	82	79	93	86	82	78	85	81	78		83	80	77		82	79	77	76
7	91	83	78	75	90	83	78	75	81	77	74		80	77	74		79	76	74	72
8	88	80	75	72	86	79	75	71	78	74	71		77	74	71		76	73	71	70
9	85	77	72	69	84	76	72	69	75	71	68		75	71	68		74	70	68	67
10	82	74	69	66	81	73	69	66	73	69	66		72	68	66		71	68	65	64

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P243931

CATALOG NUMBER: LD8B15D010 ER8B15927 8LBN0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	319.5	27.2
10°-20°	371.2	31.6
20°-30°	320.4	27.3
30°-40°	139.0	11.8
40°-50°	21.8	1.9
50°-60°	1.6	0.1
60°-70°	0.8	0.1
70°-80°	0.9	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1011.1	86.0
0°-40°	1150.1	97.8
0°-60°	1173.5	99.8
0°-90°	1175.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1175.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5760	
5°	3985	319
15°	1287	371
25°	705	320
35°	197	139
45°	23	22
55°	2	2
65°	2	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P243931

CATALOG NUMBER: LD8B15D010 ER8B15927 8LBN0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	5759.8
2.5°	5201.2
5°	3985.2
7.5°	2842.2
10°	2073.2
12.5°	1590.8
15°	1286.6
17.5°	1082.0
20°	930.2
22.5°	800.6
25°	705.3
27.5°	604.8
30°	485.2
32.5°	337.3
35°	197.0
37.5°	110.0
40°	64.2
42.5°	39.8
45°	22.7
47.5°	18.3
50°	4.8
52.5°	2.4
55°	1.6
57.5°	0.8
60°	0.0
62.5°	0.4
65°	1.6
67.5°	1.2
70°	0.4
72.5°	2.0
75°	0.8
77.5°	0.0
80°	0.8
82.5°	0.4
85°	0.0
87.5°	0.8
90°	0.0

(END OF REPORT)