

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244022

Luminaire Tested: **LD8B20D010 ER8B20830 8LBSOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244022
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-12)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B20D010 ER8B20830 8LBSOLI
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2357.0 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.24
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244022

CATALOG NUMBER: LD8B20D010 ER8B20830 8LBSOLI

Luminous Intensity Polar Plot





TEST NUMBER: P244022

CATALOG NUMBER: LD8B20D010 ER8B20830 8LBSOLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	99	95	91	103	98	93	90	94	91	88	91	88	86	88	86	84	82
3	98	91	85	80	96	89	84	79	86	82	78	84	80	77	82	78	75	74
4	92	83	76	71	90	82	75	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	63	84	75	68	63	73	67	63	71	66	62	69	65	61	60
6	80	70	62	57	79	69	62	57	67	61	56	66	60	56	64	59	56	54
7	75	64	57	52	74	63	56	52	62	56	51	61	55	51	59	54	51	49
8	71	59	52	47	69	58	52	47	57	51	47	56	51	46	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42	41
10	62	51	44	39	61	50	44	39	50	43	39	49	43	39	48	43	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40525
5°	40698
10°	41360
15°	42408
20°	43146
25°	43194
30°	41859
35°	38326
40°	33306
45°	26357
50°	17093
55°	8543
60°	3583
65°	1576
70°	487
75°	238
80°	249
85°	248



TEST NUMBER: P244022

CATALOG NUMBER: LD8B20D010 ER8B20830 8LBSOLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.7	5.3
10°-20°	375.4	15.9
20°-30°	581.5	24.7
30°-40°	631.5	26.8
40°-50°	458.9	19.5
50°-60°	156.0	6.6
60°-70°	24.8	1.1
70°-80°	2.7	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1082.5	45.9
0°-40°	1714.1	72.7
0°-60°	2328.9	98.8
0°-90°	2357.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2357.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1314	
5°	1315	126
15°	1328	375
25°	1270	581
35°	1018	632
45°	604	459
55°	159	156
65°	22	25
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P244022

CATALOG NUMBER: LD8B20D010 ER8B20830 8LBSOLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1314.2
2.5°	1314.2
5°	1314.8
7.5°	1316.9
10°	1320.9
12.5°	1325.6
15°	1328.4
17.5°	1325.6
20°	1314.8
22.5°	1295.2
25°	1269.5
27.5°	1231.0
30°	1175.6
32.5°	1101.9
35°	1018.1
37.5°	926.8
40°	827.4
42.5°	719.9
45°	604.4
47.5°	480.0
50°	356.3
52.5°	244.0
55°	158.9
57.5°	96.7
60°	58.1
62.5°	35.8
65°	21.6
67.5°	12.2
70°	5.4
72.5°	3.4
75°	2.0
77.5°	1.4
80°	1.4
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0

(END OF REPORT)