

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245318

Luminaire Tested: **LD8B20D010 ER8B20830 8LBS0WH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P245318  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B20D010 ER8B20830 8LBS0WH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 3000 CCT WITH WHEAT TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2243.0 lumens  
Efficiency: N/A  
Efficacy: 105.3 lumens/watt  
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 21.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P245318

CATALOG NUMBER: LD8B20D010 ER8B20830 8LBS0WH

### Luminous Intensity Polar Plot





TEST NUMBER: P245318

CATALOG NUMBER: LD8B20D010 ER8B20830 8LBS0WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60
6	80	70	63	57	79	69	62	57	67	61	57	66	60	56	64	60	56	54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	39178
5°	39327
10°	39823
15°	40601
20°	41180
25°	41349
30°	40082
35°	36583
40°	31648
45°	24914
50°	16071
55°	7887
60°	3244
65°	1423
70°	406
75°	155
80°	107
85°	0



TEST NUMBER: P245318

CATALOG NUMBER: LD8B20D010 ER8B20830 8LBS0WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.3	5.4
10°-20°	359.4	16.0
20°-30°	556.5	24.8
30°-40°	602.8	26.9
40°-50°	433.8	19.3
50°-60°	145.1	6.5
60°-70°	21.9	1.0
70°-80°	1.9	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1037.2	46.2
0°-40°	1640.0	73.1
0°-60°	2218.9	98.9
0°-90°	2243.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2243.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1270	
5°	1270	121
15°	1272	359
25°	1215	556
35°	972	603
45°	571	434
55°	147	145
65°	20	22
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P245318

CATALOG NUMBER: LD8B20D010 ER8B20830 8LBS0WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1270.5
2.5°	1270.5
5°	1270.5
7.5°	1271.1
10°	1271.8
12.5°	1273.1
15°	1271.8
17.5°	1266.6
20°	1254.9
22.5°	1237.4
25°	1215.3
27.5°	1180.2
30°	1125.7
32.5°	1054.3
35°	971.8
37.5°	882.9
40°	786.2
42.5°	682.3
45°	571.3
47.5°	451.2
50°	335.0
52.5°	229.8
55°	146.7
57.5°	87.6
60°	52.6
62.5°	31.8
65°	19.5
67.5°	9.7
70°	4.5
72.5°	1.9
75°	1.3
77.5°	1.3
80°	0.6
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)