

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243859

Luminaire Tested: **LD8B15D010 ER8B15927 8LBW0LI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P243859  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27941)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B15D010 ER8B15927 8LBW0LI  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 2700 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1274.6 lumens  
Efficiency: N/A  
Efficacy: 88.5 lumens/watt  
Spacing Criteria (0/90/45): 1.34 / 1.34 / 1.17  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct

Input Watts (W): 14.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P243859  
CATALOG NUMBER: LD8B15D010 ER8B15927 8LBW0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P243859

CATALOG NUMBER: LD8B15D010 ER8B15927 8LBW0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	75	72	70
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63	59	55	54
8	74	63	56	52	72	62	56	52	61	55	51		60	55	51		59	54	51	49
9	70	59	52	48	68	58	52	47	57	51	47		56	51	47		55	50	47	45
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52	47	43	42

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P243859

CATALOG NUMBER: LD8B15D010 ER8B15927 8LBW0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.5	5.8
10°-20°	243.6	19.1
20°-30°	383.4	30.1
30°-40°	364.7	28.6
40°-50°	168.1	13.2
50°-60°	38.2	3.0
60°-70°	2.5	0.2
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	700.6	55.0
0°-40°	1065.2	83.6
0°-60°	1271.5	99.8
0°-90°	1274.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1274.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	733	
5°	752	74
15°	864	244
25°	841	383
35°	598	365
45°	206	168
55°	37	38
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P243859

CATALOG NUMBER: LD8B15D010 ER8B15927 8LBW0LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	733.4
1°	733.1
2°	734.4
3°	738.6
4°	744.9
5°	752.2
6°	761.3
7°	771.1
8°	781.2
9°	793.0
10°	805.6
11°	818.1
12°	831.4
13°	844.0
14°	855.4
15°	864.4
16°	871.1
17°	875.7
18°	877.7
19°	877.4
20°	874.9
21°	870.8
22°	865.6
23°	858.6
24°	850.5
25°	840.8
26°	829.2
27°	814.6
28°	797.2
29°	776.9
30°	753.6
32.5°	683.6
35°	597.7
37.5°	498.0
40°	389.1
42.5°	287.7
45°	205.8
47.5°	145.8
50°	100.5
52.5°	64.1
55°	37.0
57.5°	18.4
60°	8.0
62.5°	3.2
65°	1.7



TEST NUMBER: P243859

CATALOG NUMBER: LD8B15D010 ER8B15927 8LBW0LI

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.0
70°	0.7
72.5°	0.7
75°	0.3
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)