

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245252

Luminaire Tested: **LD8B20D010 ER8B20835 8LBM0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245252
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201704)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B20D010 ER8B20835 8LBM0WH
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
80 CRI 3500 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2189.0 lumens
Efficiency: N/A
Efficacy: 102.8 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.83
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245252

CATALOG NUMBER: LD8B20D010 ER8B20835 8LBM0WH

Luminous Intensity Polar Plot





TEST NUMBER: P245252

CATALOG NUMBER: LD8B20D010 ER8B20835 8LBM0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74	81	77	73	79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	84735
5°	86362
10°	82341
15°	72707
20°	63005
25°	53238
30°	40008
35°	26788
40°	15003
45°	6027
50°	2087
55°	581
60°	327
65°	285
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P245252

CATALOG NUMBER: LD8B20D010 ER8B20835 8LBM0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.0	11.9
10°-20°	635.2	29.0
20°-30°	704.9	32.2
30°-40°	446.6	20.4
40°-50°	123.9	5.7
50°-60°	14.2	0.6
60°-70°	2.8	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1601.2	73.1
0°-40°	2047.8	93.5
0°-60°	2185.9	99.9
0°-90°	2189.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2189.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2748	
5°	2790	261
15°	2278	635
25°	1565	705
35°	712	447
45°	138	124
55°	11	14
65°	4	3
75°	0	0
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P245252

CATALOG NUMBER: LD8B20D010 ER8B20835 8LBM0WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2747.9
2.5°	2768.3
5°	2790.0
7.5°	2746.5
10°	2629.7
12.5°	2463.1
15°	2277.5
17.5°	2095.2
20°	1920.0
22.5°	1748.1
25°	1564.7
27.5°	1350.3
30°	1123.6
32.5°	904.1
35°	711.6
37.5°	537.8
40°	372.7
42.5°	231.8
45°	138.2
47.5°	79.5
50°	43.5
52.5°	21.3
55°	10.8
57.5°	8.1
60°	5.3
62.5°	2.8
65°	3.9
67.5°	2.0
70°	0.0
72.5°	0.6
75°	0.0
77.5°	0.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P245252

CATALOG NUMBER: LD8B20D010 ER8B20835 8LBM0WH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)