

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243884

Luminaire Tested: **LD8B20D010 ER8B20835 8LBNOLI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P243884  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-10)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B20D010 ER8B20835 8LBN0LI  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 3500 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2132.0 lumens  
Efficiency: N/A  
Efficacy: 100.1 lumens/watt  
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.32  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 21.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P243884

CATALOG NUMBER: LD8B20D010 ER8B20835 8LBN0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P243884

CATALOG NUMBER: LD8B20D010 ER8B20835 8LBN0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	100	108	104	101	99	101	99	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	91		94	92	89		92	90	88	87
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		89	86	84	83
5	98	91	86	83	96	90	86	82	88	85	82		87	84	81		85	83	80	79
6	94	87	82	79	93	86	82	78	85	81	78		83	80	77		82	79	77	76
7	91	83	78	75	90	83	78	75	81	77	74		80	77	74		79	76	74	72
8	88	80	75	72	86	79	75	71	78	74	71		77	74	71		76	73	71	70
9	85	77	72	69	84	76	72	69	75	71	68		75	71	68		74	70	68	67
10	82	74	69	66	81	73	69	66	73	69	66		72	68	66		71	68	65	64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	322098
5°	223712
10°	117724
15°	74485
20°	55353
25°	43517
30°	31330
35°	13447
40°	4686
45°	1797
50°	417
55°	156
60°	0
65°	212
70°	63
75°	167
80°	249
85°	0



TEST NUMBER: P243884

CATALOG NUMBER: LD8B20D010 ER8B20835 8LBN0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	579.4	27.2
10°-20°	673.2	31.6
20°-30°	581.0	27.3
30°-40°	252.1	11.8
40°-50°	39.5	1.9
50°-60°	2.8	0.1
60°-70°	1.5	0.1
70°-80°	1.6	0.1
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1833.6	86.0
0°-40°	2085.7	97.8
0°-60°	2128.1	99.8
0°-90°	2132.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2132.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10445	
5°	7227	579
15°	2333	673
25°	1279	581
35°	357	252
45°	41	40
55°	3	3
65°	3	2
75°	1	2
85°	0	1
90°	0	



TEST NUMBER: P243884

CATALOG NUMBER: LD8B20D010 ER8B20835 8LBN0LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	10445.4
2.5°	9432.4
5°	7227.2
7.5°	5154.4
10°	3759.7
12.5°	2884.8
15°	2333.2
17.5°	1962.3
20°	1686.8
22.5°	1451.8
25°	1279.0
27.5°	1096.8
30°	879.9
32.5°	611.7
35°	357.2
37.5°	199.6
40°	116.4
42.5°	72.3
45°	41.2
47.5°	33.3
50°	8.7
52.5°	4.3
55°	2.9
57.5°	1.4
60°	0.0
62.5°	0.7
65°	2.9
67.5°	2.2
70°	0.7
72.5°	3.6
75°	1.4
77.5°	0.0
80°	1.4
82.5°	0.7
85°	0.0
87.5°	1.4
90°	0.0

(END OF REPORT)