

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245756

Luminaire Tested: **LD8B20D010 ER8B20835 8LBS0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P245756  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-16)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B20D010 ER8B20835 8LBS0GPH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 3500 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2167.0 lumens  
Efficiency: N/A  
Efficacy: 101.7 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 21.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P245756

CATALOG NUMBER: LD8B20D010 ER8B20835 8LBS0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P245756

CATALOG NUMBER: LD8B20D010 ER8B20835 8LBS0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58
6	79	69	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53
7	74	63	56	50	73	62	55	50	61	55	50	59	54	50	58	53	49	48
8	70	58	51	46	68	57	50	46	56	50	45	55	49	45	54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	41	51	45	41	50	45	41	40
10	62	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	38357
5°	38241
10°	37862
15°	37473
20°	37081
25°	36474
30°	35479
35°	33861
40°	31483
45°	26584
50°	18047
55°	9430
60°	4231
65°	2065
70°	829
75°	500
80°	373
85°	248



TEST NUMBER: P245756

CATALOG NUMBER: LD8B20D010 ER8B20835 8LBS0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	117.1	5.4
10°-20°	331.1	15.3
20°-30°	492.9	22.7
30°-40°	560.3	25.9
40°-50°	458.2	21.1
50°-60°	170.8	7.9
60°-70°	31.2	1.4
70°-80°	4.8	0.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	941.1	43.4
0°-40°	1501.3	69.3
0°-60°	2130.3	98.3
0°-90°	2167.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2167.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1244	
5°	1235	117
15°	1174	331
25°	1072	493
35°	900	560
45°	610	458
55°	175	171
65°	28	31
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P245756

CATALOG NUMBER: LD8B20D010 ER8B20835 8LBS0GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1243.9
2.5°	1241.7
5°	1235.4
7.5°	1224.1
10°	1209.2
12.5°	1192.2
15°	1173.8
17.5°	1152.6
20°	1130.0
22.5°	1103.1
25°	1072.0
27.5°	1036.7
30°	996.4
32.5°	950.4
35°	899.5
37.5°	845.0
40°	782.1
42.5°	704.3
45°	609.6
47.5°	495.7
50°	376.2
52.5°	265.2
55°	175.4
57.5°	110.3
60°	68.6
62.5°	43.8
65°	28.3
67.5°	16.3
70°	9.2
72.5°	5.7
75°	4.2
77.5°	2.8
80°	2.1
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0

(END OF REPORT)