

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244513

Luminaire Tested: **LD8B15D010 ER8B15930 8LBS0H**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244513  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-13)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B15D010 ER8B15930 8LBS0H  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1381.0 lumens  
Efficiency: N/A  
Efficacy: 95.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244513

CATALOG NUMBER: LD8B15D010 ER8B15930 8LBS0H

### Luminous Intensity Polar Plot






TEST NUMBER: P244513

CATALOG NUMBER: LD8B15D010 ER8B15930 8LBSOH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77		83	79	76		81	78	75	73
4	91	82	75	70	89	81	75	70	79	73	69		76	72	68		74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62		70	65	61		69	64	60	59
6	80	69	61	56	78	68	61	56	66	60	56		65	59	55		63	58	55	53
7	75	63	56	51	73	63	56	51	61	55	50		60	54	50		59	54	50	48
8	70	58	51	46	69	58	51	46	57	50	46		55	50	46		54	49	45	44
9	66	54	47	42	64	53	47	42	52	46	42		51	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	37

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P244513

CATALOG NUMBER: LD8B15D010 ER8B15930 8LBSOH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	75.5	5.5
10°-20°	214.6	15.5
20°-30°	321.0	23.2
30°-40°	359.1	26.0
40°-50°	281.7	20.4
50°-60°	102.7	7.4
60°-70°	21.0	1.5
70°-80°	4.5	0.3
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	611.1	44.3
0°-40°	970.2	70.3
0°-60°	1354.6	98.1
0°-90°	1381.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1381.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	802	
5°	796	75
15°	760	215
25°	699	321
35°	578	359
45°	373	282
55°	105	103
65°	19	21
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P244513

CATALOG NUMBER: LD8B15D010 ER8B15930 8LBS0H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	801.5
2.5°	800.3
5°	795.8
7.5°	789.3
10°	780.7
12.5°	770.9
15°	760.4
17.5°	748.5
20°	734.7
22.5°	718.4
25°	699.3
27.5°	675.6
30°	647.5
32.5°	614.5
35°	577.9
37.5°	536.7
40°	491.1
42.5°	437.0
45°	373.1
47.5°	301.0
50°	226.0
52.5°	158.4
55°	105.0
57.5°	67.1
60°	43.2
62.5°	28.5
65°	19.2
67.5°	12.2
70°	7.7
72.5°	5.3
75°	4.0
77.5°	2.8
80°	2.0
82.5°	1.2
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)