

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244945

Luminaire Tested: **LD8B15D010 ER8B15930 8LBS0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244945
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-14)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B15D010 ER8B15930 8LBS0WMH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1356.4 lumens
Efficiency: N/A
Efficacy: 94.2 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244945

CATALOG NUMBER: LD8B15D010 ER8B15930 8LBS0WMH

Luminous Intensity Polar Plot






TEST NUMBER: P244945

CATALOG NUMBER: LD8B15D010 ER8B15930 8LBS0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95	94	92	91
2	105	99	94	89	102	97	92	88	94	90	86		90	87	85		88	85	83	81
3	98	90	83	78	95	88	82	78	85	80	76		83	79	75		80	77	74	72
4	91	82	75	69	89	80	74	69	78	72	68		76	71	67		74	70	66	65
5	85	74	67	62	83	73	67	61	71	65	61		70	64	60		68	63	60	58
6	79	68	61	55	77	67	60	55	66	59	55		64	58	54		63	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49		59	53	49		58	53	49	47
8	69	58	50	45	68	57	50	45	56	49	45		55	49	45		54	48	45	43
9	65	53	46	41	64	53	46	41	52	45	41		51	45	41		50	45	41	39
10	61	50	43	38	60	49	42	38	48	42	38		47	42	38		46	41	37	36

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244945

CATALOG NUMBER: LD8B15D010 ER8B15930 8LBS0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.4	5.3
10°-20°	204.9	15.1
20°-30°	305.1	22.5
30°-40°	346.6	25.6
40°-50°	283.3	20.9
50°-60°	111.0	8.2
60°-70°	25.9	1.9
70°-80°	6.2	0.5
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	582.4	42.9
0°-40°	929.0	68.5
0°-60°	1323.3	97.6
0°-90°	1356.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1356.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	769	
5°	764	72
15°	727	205
25°	664	305
35°	557	347
45°	376	283
55°	116	111
65°	24	26
75°	6	6
85°	1	1
90°	0	



TEST NUMBER: P244945

CATALOG NUMBER: LD8B15D010 ER8B15930 8LBS0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	769.1
2.5°	767.9
5°	763.7
7.5°	756.8
10°	748.3
12.5°	737.6
15°	726.6
17.5°	713.6
20°	699.3
22.5°	682.6
25°	663.9
27.5°	641.8
30°	616.9
32.5°	588.7
35°	556.9
37.5°	521.8
40°	482.7
42.5°	435.3
45°	376.2
47.5°	306.8
50°	234.6
52.5°	168.5
55°	115.5
57.5°	75.4
60°	50.6
62.5°	34.6
65°	24.1
67.5°	15.9
70°	10.6
72.5°	7.4
75°	5.7
77.5°	4.0
80°	2.5
82.5°	1.2
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)