

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243865

Luminaire Tested: **LD8B15D010 ER8B15930 8LBW0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P243865
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27941)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B15D010 ER8B15930 8LBW0LI
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1344.0 lumens
Efficiency: N/A
Efficacy: 93.3 lumens/watt
Spacing Criteria (0/90/45): 1.34 / 1.34 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P243865

CATALOG NUMBER: LD8B15D010 ER8B15930 8LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P243865

CATALOG NUMBER: LD8B15D010 ER8B15930 8LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54
8	74	63	56	52	72	62	56	52	61	55	51	60	55	51	59	54	51	49
9	70	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P243865

CATALOG NUMBER: LD8B15D010 ER8B15930 8LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.5	5.8
10°-20°	256.9	19.1
20°-30°	404.3	30.1
30°-40°	384.6	28.6
40°-50°	177.3	13.2
50°-60°	40.3	3.0
60°-70°	2.7	0.2
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	738.7	55.0
0°-40°	1123.3	83.6
0°-60°	1340.8	99.8
0°-90°	1344.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1344.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	773	
5°	793	78
15°	912	257
25°	887	404
35°	630	385
45°	217	177
55°	39	40
65°	2	3
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P243865

CATALOG NUMBER: LD8B15D010 ER8B15930 8LBW0LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	773.4
1°	772.9
2°	774.5
3°	778.9
4°	785.5
5°	793.2
6°	802.7
7°	813.1
8°	823.7
9°	836.3
10°	849.5
11°	862.7
12°	876.6
13°	890.0
14°	902.1
15°	911.6
16°	918.5
17°	923.4
18°	925.6
19°	925.2
20°	922.7
21°	918.2
22°	912.7
23°	905.3
24°	896.9
25°	886.6
26°	874.5
27°	859.0
28°	840.6
29°	819.3
30°	794.7
32.5°	720.8
35°	630.3
37.5°	525.1
40°	410.4
42.5°	303.3
45°	216.9
47.5°	153.7
50°	105.9
52.5°	67.7
55°	39.0
57.5°	19.5
60°	8.4
62.5°	3.4
65°	1.8



TEST NUMBER: P243865

CATALOG NUMBER: LD8B15D010 ER8B15930 8LBW0LI

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.1
70°	0.8
72.5°	0.8
75°	0.3
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)