

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246554

Luminaire Tested: **LD8B20D010 ER8B20840 8LBW0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246554
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-48)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B20D010 ER8B20840 8LBW0MW
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 4000 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2210.0 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246554

CATALOG NUMBER: LD8B20D010 ER8B20840 8LBW0MW

Luminous Intensity Polar Plot





TEST NUMBER: P246554

CATALOG NUMBER: LD8B20D010 ER8B20840 8LBW0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	86	83	80	78
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62
5	84	73	66	60	82	72	65	60	70	64	59	68	63	59	67	62	58	56
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47
8	69	58	50	45	68	57	50	45	56	50	45	55	49	45	54	48	45	43
9	65	54	47	42	64	53	46	42	52	46	41	51	45	41	50	45	41	40
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	45154
5°	44391
10°	42998
15°	42003
20°	41403
25°	40591
30°	38110
35°	31109
40°	19270
45°	13052
50°	11499
55°	10854
60°	10762
65°	10434
70°	9350
75°	8102
80°	6855
85°	5449



TEST NUMBER: P246554

CATALOG NUMBER: LD8B20D010 ER8B20840 8LBW0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.9	6.1
10°-20°	371.6	16.8
20°-30°	544.9	24.7
30°-40°	498.1	22.5
40°-50°	246.6	11.2
50°-60°	182.4	8.3
60°-70°	140.2	6.3
70°-80°	73.1	3.3
80°-90°	18.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1051.4	47.6
0°-40°	1549.6	70.1
0°-60°	1978.5	89.5
0°-90°	2210.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2210.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1464	
5°	1434	135
15°	1316	372
25°	1193	545
35°	826	498
45°	299	247
55°	202	182
65°	143	140
75°	68	73
85°	15	18
90°	0	



TEST NUMBER: P246554

CATALOG NUMBER: LD8B20D010 ER8B20840 8LBW0MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1464.3
2.5°	1456.6
5°	1434.1
7.5°	1404.0
10°	1373.2
12.5°	1343.0
15°	1315.7
17.5°	1289.7
20°	1261.7
22.5°	1230.2
25°	1193.0
27.5°	1141.8
30°	1070.3
32.5°	970.1
35°	826.4
37.5°	648.4
40°	478.7
42.5°	362.4
45°	299.3
47.5°	265.0
50°	239.7
52.5°	219.4
55°	201.9
57.5°	187.2
60°	174.5
62.5°	161.2
65°	143.0
67.5°	123.4
70°	103.7
72.5°	85.5
75°	68.0
77.5°	52.6
80°	38.6
82.5°	26.6
85°	15.4
87.5°	5.6
90°	0.0

(END OF REPORT)