

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245696

Luminaire Tested: **LD8B20D010 ER8B20850 8LBM0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P245696  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201629)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B20D010 ER8B20850 8LBM0GPH  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 5000 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1938.9 lumens  
Efficiency: N/A  
Efficacy: 91.0 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 21.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P245696

CATALOG NUMBER: LD8B20D010 ER8B20850 8LBM0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P245696

CATALOG NUMBER: LD8B20D010 ER8B20850 8LBM0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72	71
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	82	74	68	64	73	68	64		72	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	59	58
9	76	66	61	57	75	66	60	57	65	60	56		64	59	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	75845
5°	73918
10°	66281
15°	59018
20°	53850
25°	48903
30°	40107
35°	26407
40°	13159
45°	4893
50°	1487
55°	167
60°	99
65°	0
70°	72
75°	286
80°	0
85°	283



TEST NUMBER: P245696

CATALOG NUMBER: LD8B20D010 ER8B20850 8LBM0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	219.0	11.3
10°-20°	520.6	26.8
20°-30°	648.5	33.4
30°-40°	437.6	22.6
40°-50°	103.4	5.3
50°-60°	7.5	0.4
60°-70°	1.3	0.1
70°-80°	0.9	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1388.0	71.6
0°-40°	1825.6	94.2
0°-60°	1936.5	99.9
0°-90°	1938.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1938.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2460	
5°	2388	219
15°	1849	521
25°	1437	648
35°	702	438
45°	112	103
55°	3	7
65°	0	1
75°	2	1
85°	1	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P245696

CATALOG NUMBER: LD8B20D010 ER8B20850 8LBM0GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2459.6
2.5°	2455.7
5°	2388.0
7.5°	2266.3
10°	2116.8
12.5°	1974.4
15°	1848.7
17.5°	1740.4
20°	1641.0
22.5°	1544.8
25°	1437.3
27.5°	1297.4
30°	1126.4
32.5°	919.5
35°	701.5
37.5°	502.0
40°	326.9
42.5°	195.6
45°	112.2
47.5°	62.9
50°	31.0
52.5°	14.3
55°	3.1
57.5°	0.8
60°	1.6
62.5°	2.4
65°	0.0
67.5°	1.6
70°	0.8
72.5°	0.8
75°	2.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.8
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P245696

CATALOG NUMBER: LD8B20D010 ER8B20850 8LBM0GPH

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)