

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244760

Luminaire Tested: **LD8B20D010 ER8B20850 8LBN0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244760
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201884)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B20D010 ER8B20850 8LBN0WMH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 5000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1982.0 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.79
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244760

CATALOG NUMBER: LD8B20D010 ER8B20850 8LBN0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244760

CATALOG NUMBER: LD8B20D010 ER8B20850 8LBN0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88
3	103	97	92	89	101	96	91	88	93	89	86	91	88	85	89	86	84	82
4	98	91	86	82	97	90	85	81	88	84	80	86	82	79	84	81	79	77
5	94	86	80	76	92	85	80	76	83	78	75	81	77	74	80	76	74	72
6	89	81	75	71	88	80	75	71	79	74	70	77	73	70	76	72	69	68
7	85	76	71	67	84	76	70	66	74	70	66	73	69	66	72	68	65	64
8	81	72	66	63	80	72	66	62	71	66	62	70	65	62	69	65	62	60
9	78	68	63	59	77	68	63	59	67	62	59	66	62	59	65	61	58	57
10	74	65	59	56	73	65	59	56	64	59	56	63	59	55	62	58	55	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	89006
5°	87767
10°	80306
15°	68946
20°	58060
25°	47957
30°	35981
35°	21446
40°	10212
45°	4452
50°	2010
55°	882
60°	524
65°	285
70°	298
75°	0
80°	107
85°	495



TEST NUMBER: P244760

CATALOG NUMBER: LD8B20D010 ER8B20850 8LBN0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.8	13.2
10°-20°	601.8	30.4
20°-30°	638.5	32.2
30°-40°	364.3	18.4
40°-50°	90.3	4.6
50°-60°	17.7	0.9
60°-70°	5.3	0.3
70°-80°	1.2	0.1
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1502.1	75.8
0°-40°	1866.5	94.2
0°-60°	1974.5	99.6
0°-90°	1982.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1982.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2886	
5°	2835	262
15°	2160	602
25°	1410	639
35°	570	364
45°	102	90
55°	16	18
65°	4	5
75°	0	1
85°	1	1
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P244760

CATALOG NUMBER: LD8B20D010 ER8B20850 8LBN0WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2886.4
2.5°	2885.1
5°	2835.4
7.5°	2726.1
10°	2564.7
12.5°	2369.7
15°	2159.7
17.5°	1959.6
20°	1769.3
22.5°	1586.2
25°	1409.5
27.5°	1219.8
30°	1010.5
32.5°	785.5
35°	569.7
37.5°	392.5
40°	253.7
42.5°	160.9
45°	102.1
47.5°	66.8
50°	41.9
52.5°	25.5
55°	16.4
57.5°	13.1
60°	8.5
62.5°	7.8
65°	3.9
67.5°	3.9
70°	3.3
72.5°	1.9
75°	0.0
77.5°	0.6
80°	0.6
82.5°	1.4
85°	1.4
87.5°	0.6
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P244760

CATALOG NUMBER: LD8B20D010 ER8B20850 8LBN0WMH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)