

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244927

Luminaire Tested: **LD8B15D010 ER8B15940 8LBS0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244927
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-14)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B15D010 ER8B15940 8LBS0WMH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 4000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1462.0 lumens
Efficiency: N/A
Efficacy: 101.5 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244927

CATALOG NUMBER: LD8B15D010 ER8B15940 8LBS0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244927

CATALOG NUMBER: LD8B15D010 ER8B15940 8LBS0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	92	91
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81
3	98	90	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72
4	91	82	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66	65
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58
6	79	68	61	55	77	67	60	55	66	59	55	64	58	54	63	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49	59	53	49	58	53	49	47
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	45	43
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	25560
5°	25481
10°	25253
15°	25003
20°	24733
25°	24344
30°	23675
35°	22598
40°	20940
45°	17684
50°	12132
55°	6688
60°	3361
65°	1890
70°	1028
75°	739
80°	462
85°	318



TEST NUMBER: P244927

CATALOG NUMBER: LD8B15D010 ER8B15940 8LBS0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.0	5.3
10°-20°	220.9	15.1
20°-30°	328.8	22.5
30°-40°	373.6	25.6
40°-50°	305.4	20.9
50°-60°	119.6	8.2
60°-70°	27.9	1.9
70°-80°	6.7	0.5
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	627.8	42.9
0°-40°	1001.3	68.5
0°-60°	1426.3	97.6
0°-90°	1462.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1462.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	829	
5°	823	78
15°	783	221
25°	716	329
35°	600	374
45°	406	305
55°	124	120
65°	26	28
75°	6	7
85°	1	1
90°	0	



TEST NUMBER: P244927

CATALOG NUMBER: LD8B15D010 ER8B15940 8LBS0WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	828.9
2.5°	827.6
5°	823.2
7.5°	815.7
10°	806.5
12.5°	795.1
15°	783.2
17.5°	769.1
20°	753.7
22.5°	735.7
25°	715.5
27.5°	691.7
30°	664.9
32.5°	634.6
35°	600.3
37.5°	562.4
40°	520.2
42.5°	469.2
45°	405.5
47.5°	330.7
50°	252.9
52.5°	181.6
55°	124.4
57.5°	81.4
60°	54.5
62.5°	37.4
65°	25.9
67.5°	17.2
70°	11.4
72.5°	7.9
75°	6.2
77.5°	4.4
80°	2.6
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)