

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246452

Luminaire Tested: **LD8B20D010 ER8B20927 8LBM0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246452
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201569)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B20D010 ER8B20927 8LBM0B
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1081.0 lumens
Efficiency: N/A
Efficacy: 50.8 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246452

CATALOG NUMBER: LD8B20D010 ER8B20927 8LBM0B

Luminous Intensity Polar Plot





TEST NUMBER: P246452

CATALOG NUMBER: LD8B20D010 ER8B20927 8LBM0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | | 50 | 30 | 10 | | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | | 106 | 106 | 106 | | 102 | 102 | 102 | 100 |
| 1 | 114 | 111 | 108 | 106 | 111 | 109 | 107 | 105 | 105 | 103 | 101 | | 101 | 100 | 98 | | 98 | 97 | 96 | 94 |
| 2 | 108 | 103 | 99 | 96 | 106 | 102 | 98 | 95 | 98 | 95 | 93 | | 95 | 93 | 91 | | 93 | 91 | 89 | 87 |
| 3 | 103 | 97 | 92 | 88 | 101 | 95 | 91 | 87 | 93 | 89 | 86 | | 90 | 87 | 84 | | 88 | 85 | 83 | 81 |
| 4 | 98 | 90 | 85 | 81 | 96 | 89 | 84 | 80 | 87 | 83 | 79 | | 85 | 81 | 78 | | 83 | 80 | 77 | 76 |
| 5 | 93 | 85 | 79 | 75 | 91 | 84 | 78 | 74 | 82 | 77 | 74 | | 80 | 76 | 73 | | 79 | 75 | 72 | 71 |
| 6 | 88 | 79 | 74 | 69 | 87 | 79 | 73 | 69 | 77 | 72 | 69 | | 76 | 71 | 68 | | 74 | 71 | 68 | 66 |
| 7 | 84 | 75 | 69 | 65 | 83 | 74 | 68 | 64 | 73 | 68 | 64 | | 72 | 67 | 64 | | 70 | 66 | 63 | 62 |
| 8 | 80 | 70 | 64 | 60 | 79 | 70 | 64 | 60 | 69 | 64 | 60 | | 68 | 63 | 60 | | 67 | 63 | 60 | 58 |
| 9 | 76 | 66 | 61 | 57 | 75 | 66 | 60 | 57 | 65 | 60 | 56 | | 64 | 60 | 56 | | 63 | 59 | 56 | 55 |
| 10 | 72 | 63 | 57 | 53 | 71 | 62 | 57 | 53 | 62 | 57 | 53 | | 61 | 56 | 53 | | 60 | 56 | 53 | 52 |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P246452

CATALOG NUMBER: LD8B20D010 ER8B20927 8LBM0B

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 123.3 | 11.4 |
| 10°-20° | 286.6 | 26.5 |
| 20°-30° | 362.7 | 33.5 |
| 30°-40° | 248.8 | 23.0 |
| 40°-50° | 56.6 | 5.2 |
| 50°-60° | 2.7 | 0.3 |
| 60°-70° | 0.1 | 0.0 |
| 70°-80° | 0.2 | 0.0 |
| 80°-90° | 0.2 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 772.5 | 71.5 |
| 0°-40° | 1021.3 | 94.5 |
| 0°-60° | 1080.6 | 100.0 |
| 0°-90° | 1081.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1081.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|------|------|------|
| 0° | 1402 | |
| 5° | 1354 | 123 |
| 15° | 1016 | 287 |
| 25° | 804 | 363 |
| 35° | 402 | 249 |
| 45° | 61 | 57 |
| 55° | 1 | 3 |
| 65° | 0 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | 0 |
| 95° | 0 | 0 |
| 105° | 0 | 0 |
| 115° | 0 | 0 |
| 125° | 0 | 0 |
| 135° | 0 | 0 |
| 145° | 0 | 0 |
| 155° | 0 | 0 |
| 165° | 0 | 0 |
| 175° | 0 | 0 |
| 180° | 0 | 0 |



TEST NUMBER: P246452

CATALOG NUMBER: LD8B20D010 ER8B20927 8LBM0B

CANDELA DISTRIBUTION (FULL):

| 0° | |
|--------|--------|
| 0° | 1402.5 |
| 2.5° | 1402.5 |
| 5° | 1354.4 |
| 7.5° | 1271.8 |
| 10° | 1172.7 |
| 12.5° | 1085.5 |
| 15° | 1015.5 |
| 17.5° | 957.2 |
| 20° | 905.2 |
| 22.5° | 856.0 |
| 25° | 804.2 |
| 27.5° | 731.7 |
| 30° | 639.6 |
| 32.5° | 523.7 |
| 35° | 401.7 |
| 37.5° | 283.8 |
| 40° | 182.8 |
| 42.5° | 107.6 |
| 45° | 61.0 |
| 47.5° | 32.6 |
| 50° | 16.8 |
| 52.5° | 2.9 |
| 55° | 1.0 |
| 57.5° | 0.4 |
| 60° | 0.0 |
| 62.5° | 0.0 |
| 65° | 0.4 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.4 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.4 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.4 |
| 90° | 0.0 |
| 92.5° | 0.0 |
| 95° | 0.0 |
| 97.5° | 0.0 |
| 100° | 0.0 |
| 102.5° | 0.0 |
| 105° | 0.0 |
| 107.5° | 0.0 |
| 110° | 0.0 |



TEST NUMBER: P246452

CATALOG NUMBER: LD8B20D010 ER8B20927 8LBM0B

CANDELA DISTRIBUTION (continued):

| | 0° |
|--------|-----|
| 112.5° | 0.0 |
| 115° | 0.0 |
| 117.5° | 0.0 |
| 120° | 0.0 |
| 122.5° | 0.0 |
| 125° | 0.0 |
| 127.5° | 0.0 |
| 130° | 0.0 |
| 132.5° | 0.0 |
| 135° | 0.0 |
| 137.5° | 0.0 |
| 140° | 0.0 |
| 142.5° | 0.0 |
| 145° | 0.0 |
| 147.5° | 0.0 |
| 150° | 0.0 |
| 152.5° | 0.0 |
| 155° | 0.0 |
| 157.5° | 0.0 |
| 160° | 0.0 |
| 162.5° | 0.0 |
| 165° | 0.0 |
| 167.5° | 0.0 |
| 170° | 0.0 |
| 172.5° | 0.0 |
| 175° | 0.0 |
| 177.5° | 0.0 |
| 180° | 0.0 |

(END OF REPORT)