

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245575

Luminaire Tested: **LD8B15D010 ER8B15940 8LBW0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245575
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-46)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B15D010 ER8B15940 8LBW0GPH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 4000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1227.0 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245575

CATALOG NUMBER: LD8B15D010 ER8B15940 8LBW0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245575

CATALOG NUMBER: LD8B15D010 ER8B15940 8LBW0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100		100	98	97		96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89		93	90	87		90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84	81	78	76
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78	74	71	70
5	88	79	72	67	87	78	72	67	76	71	66		74	70	66		73	69	65	64
6	83	73	66	61	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		65	59	56		63	59	55	54
8	74	63	56	52	73	63	56	52	61	56	51		60	55	51		59	55	51	49
9	70	59	52	48	69	58	52	48	57	52	48		57	51	47		56	51	47	46
10	66	55	49	44	65	55	49	44	54	48	44		53	48	44		52	47	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	29461
5°	28766
10°	27865
15°	27461
20°	27138
25°	26552
30°	24871
35°	20309
40°	12124
45°	7283
50°	5248
55°	3570
60°	2239
65°	1102
70°	279
75°	107
80°	71
85°	0



TEST NUMBER: P245575

CATALOG NUMBER: LD8B15D010 ER8B15940 8LBW0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.4	7.1
10°-20°	242.8	19.8
20°-30°	356.5	29.1
30°-40°	323.2	26.3
40°-50°	138.3	11.3
50°-60°	61.2	5.0
60°-70°	16.3	1.3
70°-80°	1.3	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	686.6	56.0
0°-40°	1009.8	82.3
0°-60°	1209.3	98.6
0°-90°	1227.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1227.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	955	
5°	929	87
15°	860	243
25°	780	356
35°	540	323
45°	167	138
55°	66	61
65°	15	16
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P245575

CATALOG NUMBER: LD8B15D010 ER8B15940 8LBW0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	955.4
2.5°	947.9
5°	929.3
7.5°	908.0
10°	889.9
12.5°	874.8
15°	860.2
17.5°	844.7
20°	827.0
22.5°	806.1
25°	780.4
27.5°	745.9
30°	698.5
32.5°	632.1
35°	539.5
37.5°	418.1
40°	301.2
42.5°	217.5
45°	167.0
47.5°	134.7
50°	109.4
52.5°	86.8
55°	66.4
57.5°	49.6
60°	36.3
62.5°	25.2
65°	15.1
67.5°	6.6
70°	3.1
72.5°	1.8
75°	0.9
77.5°	0.4
80°	0.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)