

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244508

Luminaire Tested: **LD8B20D010 ER8B20927 8LBS0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244508
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-13)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B20D010 ER8B20927 8LBS0H
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1861.9 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244508

CATALOG NUMBER: LD8B20D010 ER8B20927 8LBS0H

Luminous Intensity Polar Plot





TEST NUMBER: P244508

CATALOG NUMBER: LD8B20D010 ER8B20927 8LBS0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77		83	79	76		81	78	75	73
4	91	82	75	70	89	81	75	70	79	73	69		76	72	68		74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62		70	65	61		69	64	60	59
6	80	69	61	56	78	68	61	56	66	60	56		65	59	55		63	58	55	53
7	75	63	56	51	73	63	56	51	61	55	50		60	54	50		59	54	50	48
8	70	58	51	46	68	58	51	46	57	50	46		55	50	46		54	49	45	44
9	66	54	47	42	64	53	47	42	52	46	42		51	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244508

CATALOG NUMBER: LD8B20D010 ER8B20927 8LBSOH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.8	5.5
10°-20°	289.3	15.5
20°-30°	432.8	23.2
30°-40°	484.1	26.0
40°-50°	379.8	20.4
50°-60°	138.6	7.4
60°-70°	28.3	1.5
70°-80°	6.1	0.3
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	823.9	44.2
0°-40°	1307.9	70.2
0°-60°	1826.3	98.1
0°-90°	1861.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1861.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1080	
5°	1073	102
15°	1025	289
25°	943	433
35°	779	484
45°	503	380
55°	142	139
65°	26	28
75°	6	6
85°	1	1
90°	0	



TEST NUMBER: P244508

CATALOG NUMBER: LD8B20D010 ER8B20927 8LBS0H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1080.4
2.5°	1078.9
5°	1072.8
7.5°	1064.0
10°	1052.6
12.5°	1039.3
15°	1025.1
17.5°	1009.1
20°	990.4
22.5°	968.5
25°	942.6
27.5°	910.8
30°	873.0
32.5°	828.4
35°	779.1
37.5°	723.6
40°	662.2
42.5°	589.2
45°	502.9
47.5°	405.8
50°	304.8
52.5°	213.5
55°	141.6
57.5°	90.6
60°	58.2
62.5°	38.5
65°	25.8
67.5°	16.4
70°	10.5
72.5°	7.1
75°	5.5
77.5°	3.8
80°	2.7
82.5°	1.7
85°	1.1
87.5°	0.6
90°	0.0

(END OF REPORT)