

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244717

Luminaire Tested: **LD8B15D010 ER8B15950 8LBW0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244717  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B15D010 ER8B15950 8LBW0WMH  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
90 CRI 5000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1377.0 lumens  
Efficiency: N/A  
Efficacy: 95.6 lumens/watt  
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244717

CATALOG NUMBER: LD8B15D010 ER8B15950 8LBW0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P244717

CATALOG NUMBER: LD8B15D010 ER8B15950 8LBW0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	30772
5°	30152
10°	29198
15°	28805
20°	28635
25°	28271
30°	26751
35°	22063
40°	13775
45°	8861
50°	6870
55°	5290
60°	4009
65°	2605
70°	1118
75°	548
80°	249
85°	177



TEST NUMBER: P244717

CATALOG NUMBER: LD8B15D010 ER8B15950 8LBW0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	91.6	6.7
10°-20°	254.9	18.5
20°-30°	379.7	27.6
30°-40°	352.6	25.6
40°-50°	166.6	12.1
50°-60°	89.5	6.5
60°-70°	35.9	2.6
70°-80°	5.6	0.4
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	726.2	52.7
0°-40°	1078.8	78.3
0°-60°	1334.9	96.9
0°-90°	1377.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1377.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	998	
5°	974	92
15°	902	255
25°	831	380
35°	586	353
45°	203	167
55°	98	89
65°	36	36
75°	5	6
85°	0	1
90°	0	



TEST NUMBER: P244717

CATALOG NUMBER: LD8B15D010 ER8B15950 8LBW0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	997.9
2.5°	991.1
5°	974.1
7.5°	952.6
10°	932.5
12.5°	916.0
15°	902.3
17.5°	888.1
20°	872.6
22.5°	854.7
25°	830.9
27.5°	797.5
30°	751.3
32.5°	683.6
35°	586.1
37.5°	461.7
40°	342.2
42.5°	254.9
45°	203.2
47.5°	169.8
50°	143.2
52.5°	119.4
55°	98.4
57.5°	80.1
60°	65.0
62.5°	50.8
65°	35.7
67.5°	21.0
70°	12.4
72.5°	7.3
75°	4.6
77.5°	2.7
80°	1.4
82.5°	0.9
85°	0.5
87.5°	0.0
90°	0.0

(END OF REPORT)