

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245282

Luminaire Tested: **LD8B20D010 ER8B20935 8LBM0WH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P245282  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201704)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B20D010 ER8B20935 8LBM0WH  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT  
90 CRI 3500 CCT WITH WHEAT TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1867.1 lumens  
Efficiency: N/A  
Efficacy: 87.7 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.83  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 21.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P245282

CATALOG NUMBER: LD8B20D010 ER8B20935 8LBM0WH

### Luminous Intensity Polar Plot





TEST NUMBER: P245282

CATALOG NUMBER: LD8B20D010 ER8B20935 8LBM0WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74	81	77	73	79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	72271
5°	73658
10°	70230
15°	62013
20°	53738
25°	45409
30°	34122
35°	22850
40°	12797
45°	5142
50°	1780
55°	495
60°	278
65°	241
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P245282

CATALOG NUMBER: LD8B20D010 ER8B20935 8LBM0WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	222.6	11.9
10°-20°	541.8	29.0
20°-30°	601.2	32.2
30°-40°	380.9	20.4
40°-50°	105.7	5.7
50°-60°	12.1	0.6
60°-70°	2.4	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1365.7	73.1
0°-40°	1746.6	93.5
0°-60°	1864.4	99.9
0°-90°	1867.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1867.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2344	
5°	2380	223
15°	1942	542
25°	1335	601
35°	607	381
45°	118	106
55°	9	12
65°	3	2
75°	0	0
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P245282

CATALOG NUMBER: LD8B20D010 ER8B20935 8LBM0WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2343.7
2.5°	2361.1
5°	2379.6
7.5°	2342.5
10°	2242.9
12.5°	2100.8
15°	1942.5
17.5°	1787.0
20°	1637.6
22.5°	1491.0
25°	1334.6
27.5°	1151.7
30°	958.3
32.5°	771.1
35°	607.0
37.5°	458.7
40°	317.9
42.5°	197.7
45°	117.9
47.5°	67.8
50°	37.1
52.5°	18.2
55°	9.2
57.5°	6.9
60°	4.5
62.5°	2.4
65°	3.3
67.5°	1.7
70°	0.0
72.5°	0.5
75°	0.0
77.5°	0.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P245282

CATALOG NUMBER: LD8B20D010 ER8B20935 8LBM0WH

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)