

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243914

Luminaire Tested: **LD8B20D010 ER8B20935 8LBNOLI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P243914  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-10)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B20D010 ER8B20935 8LBN0LI  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
90 CRI 3500 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1818.0 lumens  
Efficiency: N/A  
Efficacy: 85.4 lumens/watt  
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.32  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 21.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P243914

CATALOG NUMBER: LD8B20D010 ER8B20935 8LBN0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P243914

CATALOG NUMBER: LD8B20D010 ER8B20935 8LBN0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	100	108	104	101	99	101	99	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	91		94	92	89		92	90	88	87
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		89	86	84	83
5	98	91	86	83	96	90	86	82	88	85	82		87	84	81		85	83	80	79
6	94	87	82	79	93	86	82	78	85	81	78		83	80	77		82	79	77	76
7	91	83	78	75	90	83	78	75	81	77	74		80	77	74		79	76	74	72
8	88	80	75	72	86	79	75	71	78	74	71		77	74	71		76	73	71	70
9	85	77	72	69	84	76	72	69	75	71	68		75	71	68		74	70	68	67
10	82	74	69	66	81	73	69	66	73	69	66		72	68	66		71	68	65	64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	274659
5°	190764
10°	100383
15°	63513
20°	47202
25°	37107
30°	26716
35°	11466
40°	3997
45°	1531
50°	355
55°	134
60°	0
65°	182
70°	54
75°	143
80°	213
85°	0



TEST NUMBER: P243914

CATALOG NUMBER: LD8B20D010 ER8B20935 8LBN0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	494.1	27.2
10°-20°	574.0	31.6
20°-30°	495.4	27.3
30°-40°	215.0	11.8
40°-50°	33.7	1.9
50°-60°	2.4	0.1
60°-70°	1.3	0.1
70°-80°	1.4	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1563.6	86.0
0°-40°	1778.5	97.8
0°-60°	1814.7	99.8
0°-90°	1818.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1818.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8907	
5°	6163	494
15°	1990	574
25°	1091	495
35°	305	215
45°	35	34
55°	2	2
65°	2	1
75°	1	1
85°	0	1
90°	0	



TEST NUMBER: P243914

CATALOG NUMBER: LD8B20D010 ER8B20935 8LBN0LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8907.0
2.5°	8043.2
5°	6162.8
7.5°	4395.2
10°	3205.9
12.5°	2459.9
15°	1989.5
17.5°	1673.3
20°	1438.4
22.5°	1238.0
25°	1090.6
27.5°	935.3
30°	750.3
32.5°	521.6
35°	304.6
37.5°	170.2
40°	99.3
42.5°	61.7
45°	35.1
47.5°	28.4
50°	7.4
52.5°	3.7
55°	2.5
57.5°	1.2
60°	0.0
62.5°	0.6
65°	2.5
67.5°	1.8
70°	0.6
72.5°	3.1
75°	1.2
77.5°	0.0
80°	1.2
82.5°	0.6
85°	0.0
87.5°	1.2
90°	0.0

(END OF REPORT)