

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244490

Luminaire Tested: **LD8B20D010 ER8B20935 8LBS0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244490
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-13)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B20D010 ER8B20935 8LBS0H
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 3500 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2027.0 lumens
Efficiency: N/A
Efficacy: 95.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244490

CATALOG NUMBER: LD8B20D010 ER8B20935 8LBS0H

Luminous Intensity Polar Plot





TEST NUMBER: P244490

CATALOG NUMBER: LD8B20D010 ER8B20935 8LBSOH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77		83	79	76		81	78	75	73
4	91	82	75	70	89	81	75	70	79	73	69		76	72	68		74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62		70	65	61		69	64	60	59
6	80	69	61	56	78	68	61	56	66	60	56		65	59	55		63	58	55	53
7	75	63	56	51	73	63	56	51	61	55	50		60	54	50		59	54	50	48
8	70	58	51	46	68	58	51	46	57	50	46		55	50	46		54	49	45	44
9	66	54	47	42	64	53	47	42	52	46	42		51	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36273
5°	36154
10°	35877
15°	35627
20°	35385
25°	34919
30°	33841
35°	31930
40°	29019
45°	23876
50°	15913
55°	8290
60°	3910
65°	2050
70°	1028
75°	715
80°	533
85°	425



TEST NUMBER: P244490

CATALOG NUMBER: LD8B20D010 ER8B20935 8LBSOH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.8	5.5
10°-20°	315.0	15.5
20°-30°	471.2	23.2
30°-40°	527.0	26.0
40°-50°	413.4	20.4
50°-60°	150.8	7.4
60°-70°	30.7	1.5
70°-80°	6.6	0.3
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	896.9	44.2
0°-40°	1424.0	70.2
0°-60°	1988.3	98.1
0°-90°	2027.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2027.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1176	
5°	1168	111
15°	1116	315
25°	1026	471
35°	848	527
45°	548	413
55°	154	151
65°	28	31
75°	6	7
85°	1	1
90°	0	



TEST NUMBER: P244490

CATALOG NUMBER: LD8B20D010 ER8B20935 8LBS0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1176.3
2.5°	1174.5
5°	1168.0
7.5°	1158.4
10°	1145.8
12.5°	1131.5
15°	1116.0
17.5°	1098.6
20°	1078.3
22.5°	1054.4
25°	1026.3
27.5°	991.6
30°	950.4
32.5°	902.0
35°	848.2
37.5°	787.8
40°	720.9
42.5°	641.4
45°	547.5
47.5°	441.7
50°	331.7
52.5°	232.5
55°	154.2
57.5°	98.6
60°	63.4
62.5°	41.8
65°	28.1
67.5°	17.9
70°	11.4
72.5°	7.8
75°	6.0
77.5°	4.2
80°	3.0
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)