

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244513

Luminaire Tested: **LD8B15D010 ER8B159730 8LBS0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244513
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-13)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B15D010 ER8B159730 8LBS0H
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1231.9 lumens
Efficiency: N/A
Efficacy: 85.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244513

CATALOG NUMBER: LD8B15D010 ER8B159730 8LBS0H

Luminous Intensity Polar Plot





TEST NUMBER: P244513

CATALOG NUMBER: LD8B15D010 ER8B159730 8LBS0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73
4	91	82	75	70	89	81	75	70	79	73	69	76	72	68	74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62	70	65	61	69	64	60	59
6	80	69	61	56	78	68	61	56	66	60	56	65	59	55	63	58	55	53
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244513

CATALOG NUMBER: LD8B15D010 ER8B159730 8LBS0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.3	5.5
10°-20°	191.4	15.5
20°-30°	286.4	23.2
30°-40°	320.3	26.0
40°-50°	251.3	20.4
50°-60°	91.7	7.4
60°-70°	18.7	1.5
70°-80°	4.0	0.3
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	545.2	44.3
0°-40°	865.5	70.3
0°-60°	1208.4	98.1
0°-90°	1231.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1231.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	715	
5°	710	67
15°	678	191
25°	624	286
35°	516	320
45°	333	251
55°	94	92
65°	17	19
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P244513

CATALOG NUMBER: LD8B15D010 ER8B159730 8LBS0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	715.0
2.5°	713.9
5°	709.9
7.5°	704.1
10°	696.4
12.5°	687.7
15°	678.3
17.5°	667.7
20°	655.4
22.5°	640.9
25°	623.8
27.5°	602.7
30°	577.6
32.5°	548.2
35°	515.5
37.5°	478.8
40°	438.1
42.5°	389.8
45°	332.8
47.5°	268.5
50°	201.6
52.5°	141.3
55°	93.7
57.5°	59.9
60°	38.5
62.5°	25.4
65°	17.1
67.5°	10.9
70°	6.9
72.5°	4.7
75°	3.6
77.5°	2.5
80°	1.8
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)