

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245792

Luminaire Tested: **LD8B20D010 ER8B20940 8LBS0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245792
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-16)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B20D010 ER8B20940 8LBS0GPH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 4000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1930.0 lumens
Efficiency: N/A
Efficacy: 90.6 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245792

CATALOG NUMBER: LD8B20D010 ER8B20940 8LBS0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245792

CATALOG NUMBER: LD8B20D010 ER8B20940 8LBS0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77		83	79	76		81	77	74	73
4	91	82	75	70	89	81	74	69	78	73	69		76	72	68		74	70	67	65
5	85	75	68	62	83	74	67	62	72	66	61		70	65	61		68	64	60	58
6	79	69	61	56	78	68	61	56	66	60	55		64	59	55		63	58	54	53
7	74	63	56	50	73	62	55	50	61	55	50		59	54	50		58	53	49	48
8	70	58	51	46	68	57	50	46	56	50	45		55	49	45		54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	41		51	45	41		50	45	41	40
10	62	50	43	38	60	49	43	38	48	42	38		48	42	38		47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	34160
5°	34059
10°	33723
15°	33377
20°	33025
25°	32486
30°	31597
35°	30157
40°	28041
45°	23675
50°	16076
55°	8398
60°	3768
65°	1839
70°	739
75°	453
80°	337
85°	212



TEST NUMBER: P245792

CATALOG NUMBER: LD8B20D010 ER8B20940 8LBS0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.3	5.4
10°-20°	294.9	15.3
20°-30°	439.0	22.7
30°-40°	499.0	25.9
40°-50°	408.1	21.1
50°-60°	152.1	7.9
60°-70°	27.8	1.4
70°-80°	4.3	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	838.1	43.4
0°-40°	1337.2	69.3
0°-60°	1897.3	98.3
0°-90°	1930.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1930.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1108	
5°	1100	104
15°	1046	295
25°	955	439
35°	801	499
45°	543	408
55°	156	152
65°	25	28
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P245792

CATALOG NUMBER: LD8B20D010 ER8B20940 8LBS0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1107.8
2.5°	1105.9
5°	1100.3
7.5°	1090.2
10°	1077.0
12.5°	1061.8
15°	1045.5
17.5°	1026.6
20°	1006.4
22.5°	982.5
25°	954.8
27.5°	923.3
30°	887.4
32.5°	846.5
35°	801.1
37.5°	752.6
40°	696.6
42.5°	627.3
45°	542.9
47.5°	441.5
50°	335.1
52.5°	236.2
55°	156.2
57.5°	98.2
60°	61.1
62.5°	39.0
65°	25.2
67.5°	14.5
70°	8.2
72.5°	5.0
75°	3.8
77.5°	2.5
80°	1.9
82.5°	0.6
85°	0.6
87.5°	0.0
90°	0.0

(END OF REPORT)