

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244502

Luminaire Tested: **LD8B20D010 ER8B20950 8LBS0H**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244502  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-13)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B20D010 ER8B20950 8LBS0H  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
90 CRI 5000 CCT WITH SEMI-SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2191.0 lumens  
Efficiency: N/A  
Efficacy: 102.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 21.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244502  
CATALOG NUMBER: LD8B20D010 ER8B20950 8LBS0H

### Luminous Intensity Polar Plot





TEST NUMBER: P244502

CATALOG NUMBER: LD8B20D010 ER8B20950 8LBS0H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77		83	79	76		81	78	75	73
4	91	82	75	70	89	81	75	70	79	73	69		76	72	68		74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62		70	65	61		69	64	60	59
6	80	69	61	56	78	68	61	56	66	60	56		65	59	55		63	58	55	53
7	75	63	56	51	73	63	56	51	61	55	50		60	54	50		59	54	50	48
8	70	58	51	46	68	58	51	46	57	50	46		55	50	46		54	49	45	44
9	66	54	47	42	64	53	47	42	52	46	42		51	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	39208
5°	39080
10°	38780
15°	38507
20°	38246
25°	37743
30°	36579
35°	34512
40°	31366
45°	25808
50°	17203
55°	8962
60°	4225
65°	2218
70°	1109
75°	774
80°	568
85°	460



TEST NUMBER: P244502

CATALOG NUMBER: LD8B20D010 ER8B20950 8LBS0H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	119.8	5.5
10°-20°	340.4	15.5
20°-30°	509.3	23.2
30°-40°	569.6	26.0
40°-50°	446.9	20.4
50°-60°	163.1	7.4
60°-70°	33.3	1.5
70°-80°	7.1	0.3
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	969.5	44.2
0°-40°	1539.1	70.2
0°-60°	2149.1	98.1
0°-90°	2191.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2191.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1272	
5°	1262	120
15°	1206	340
25°	1109	509
35°	917	570
45°	592	447
55°	167	163
65°	30	33
75°	6	7
85°	1	1
90°	0	



TEST NUMBER: P244502

CATALOG NUMBER: LD8B20D010 ER8B20950 8LBS0H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1271.5
2.5°	1269.6
5°	1262.5
7.5°	1252.1
10°	1238.5
12.5°	1223.0
15°	1206.2
17.5°	1187.5
20°	1165.5
22.5°	1139.7
25°	1109.3
27.5°	1071.9
30°	1027.3
32.5°	974.9
35°	916.8
37.5°	851.5
40°	779.2
42.5°	693.2
45°	591.8
47.5°	477.5
50°	358.6
52.5°	251.3
55°	166.7
57.5°	106.6
60°	68.5
62.5°	45.2
65°	30.4
67.5°	19.4
70°	12.3
72.5°	8.4
75°	6.5
77.5°	4.5
80°	3.2
82.5°	1.9
85°	1.3
87.5°	0.6
90°	0.0

(END OF REPORT)