

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244070

Luminaire Tested: **LD8B20D010 ER8B20950 8LBSOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244070
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-12)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B20D010 ER8B20950 8LBSOLI
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 5000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2261.0 lumens
Efficiency: N/A
Efficacy: 106.1 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.24
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244070

CATALOG NUMBER: LD8B20D010 ER8B20950 8LBSOLI

Luminous Intensity Polar Plot





TEST NUMBER: P244070

CATALOG NUMBER: LD8B20D010 ER8B20950 8LBSOLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	99	95	91	103	98	93	90	94	91	88		91	88	86		88	86	84	82
3	98	91	85	80	96	89	84	79	86	82	78		84	80	77		82	78	75	74
4	92	83	76	71	90	82	75	71	79	74	70		77	73	69		75	71	68	66
5	86	76	69	63	84	75	68	63	73	67	63		71	66	62		69	65	61	60
6	80	70	62	57	79	69	62	57	67	61	56		66	60	56		64	59	56	54
7	75	64	57	52	74	63	56	52	62	56	51		61	55	51		59	54	51	49
8	71	59	52	47	69	58	52	47	57	51	47		56	51	46		55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43		52	47	43		51	46	42	41
10	62	51	44	39	61	50	44	39	50	43	39		49	43	39		48	43	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	38872
5°	39042
10°	39675
15°	40681
20°	41390
25°	41435
30°	40154
35°	36763
40°	31950
45°	25280
50°	16392
55°	8193
60°	3441
65°	1518
70°	469
75°	226
80°	231
85°	212



TEST NUMBER: P244070

CATALOG NUMBER: LD8B20D010 ER8B20950 8LBSOLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.6	5.3
10°-20°	360.1	15.9
20°-30°	557.8	24.7
30°-40°	605.8	26.8
40°-50°	440.2	19.5
50°-60°	149.6	6.6
60°-70°	23.9	1.1
70°-80°	2.5	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1038.5	45.9
0°-40°	1644.3	72.7
0°-60°	2234.1	98.8
0°-90°	2261.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2261.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1261	
5°	1261	121
15°	1274	360
25°	1218	558
35°	977	606
45°	580	440
55°	152	150
65°	21	24
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P244070

CATALOG NUMBER: LD8B20D010 ER8B20950 8LBSOLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1260.6
2.5°	1260.6
5°	1261.3
7.5°	1263.2
10°	1267.1
12.5°	1271.7
15°	1274.3
17.5°	1271.7
20°	1261.3
22.5°	1242.5
25°	1217.8
27.5°	1180.9
30°	1127.7
32.5°	1057.0
35°	976.6
37.5°	889.1
40°	793.7
42.5°	690.6
45°	579.7
47.5°	460.4
50°	341.7
52.5°	234.1
55°	152.4
57.5°	92.7
60°	55.8
62.5°	34.4
65°	20.8
67.5°	11.7
70°	5.2
72.5°	3.2
75°	1.9
77.5°	1.3
80°	1.3
82.5°	0.6
85°	0.6
87.5°	0.0
90°	0.0

(END OF REPORT)