

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244370

Luminaire Tested: **LD8B20D010 ER8B209730 8LBN0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244370
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27944)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B20D010 ER8B209730 8LBN0H
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1482.0 lumens
Efficiency: N/A
Efficacy: 69.6 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.79
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244370

CATALOG NUMBER: LD8B20D010 ER8B209730 8LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P244370

CATALOG NUMBER: LD8B20D010 ER8B209730 8LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	86	83	82
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	69	67
7	85	76	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	58		64	60	57	56
10	74	64	59	55	73	64	58	55	63	58	55		62	58	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244370

CATALOG NUMBER: LD8B20D010 ER8B209730 8LBN0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	190.2	12.8
10°-20°	425.1	28.7
20°-30°	483.4	32.6
30°-40°	283.9	19.2
40°-50°	76.2	5.1
50°-60°	18.1	1.2
60°-70°	4.1	0.3
70°-80°	0.9	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1098.8	74.1
0°-40°	1382.6	93.3
0°-60°	1476.9	99.7
0°-90°	1482.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1482.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2262	
5°	2102	190
15°	1520	425
25°	1067	483
35°	442	284
45°	91	76
55°	18	18
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P244370

CATALOG NUMBER: LD8B20D010 ER8B209730 8LBN0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2262.3
1°	2249.8
2°	2226.8
3°	2194.2
4°	2152.2
5°	2102.1
6°	2045.6
7°	1981.5
8°	1917.4
9°	1852.9
10°	1791.3
11°	1731.3
12°	1674.7
13°	1622.1
14°	1569.6
15°	1520.5
16°	1472.5
17°	1424.9
18°	1378.9
19°	1332.3
20°	1286.8
21°	1241.3
22°	1197.7
23°	1154.7
24°	1110.6
25°	1066.6
26°	1021.0
27°	971.5
28°	919.4
29°	862.4
30°	800.8
32.5°	628.1
35°	441.9
37.5°	291.3
40°	190.7
42.5°	131.6
45°	91.1
47.5°	62.6
50°	41.5
52.5°	27.0
55°	18.0
57.5°	12.0
60°	8.0
62.5°	5.5
65°	4.0



TEST NUMBER: P244370

CATALOG NUMBER: LD8B20D010 ER8B209730 8LBN0H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	2.5
70°	1.5
72.5°	1.0
75°	1.0
77.5°	0.5
80°	0.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)