

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250614

Luminaire Tested: **LD8B150D010 ER8B150927 8LBM0B**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250614  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13928)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B150D010 ER8B150927 8LBM0B  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 2700 CCT WITH SPECULAR BLACK TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8010.0 lumens  
Efficiency: N/A  
Efficacy: 50.5 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.87  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 158.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250614

CATALOG NUMBER: LD8B150D010 ER8B150927 8LBM0B

### Luminous Intensity Polar Plot





TEST NUMBER: P250614

CATALOG NUMBER: LD8B150D010 ER8B150927 8LBM0B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72	71
6	88	79	74	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	83	74	68	64	73	68	64		72	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	60	58
9	76	66	61	57	75	66	60	57	65	60	56		64	60	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P250614

CATALOG NUMBER: LD8B150D010 ER8B150927 8LBM0B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	912.9	11.4
10°-20°	2120.0	26.5
20°-30°	2689.6	33.6
30°-40°	1842.6	23.0
40°-50°	419.9	5.2
50°-60°	20.9	0.3
60°-70°	1.0	0.0
70°-80°	1.5	0.0
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5722.5	71.4
0°-40°	7565.1	94.4
0°-60°	8005.9	99.9
0°-90°	8010.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8010.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10393	
5°	10037	913
15°	7525	2120
25°	5957	2690
35°	2977	1843
45°	453	420
55°	8	21
65°	4	1
75°	0	2
85°	0	2
90°	0	



TEST NUMBER: P250614

CATALOG NUMBER: LD8B150D010 ER8B150927 8LBM0B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	10393.2
1°	10447.4
2°	10428.0
3°	10350.7
4°	10218.9
5°	10037.1
6°	9816.4
7°	9561.0
8°	9278.4
9°	8976.5
10°	8690.1
11°	8426.8
12°	8144.3
13°	7939.1
14°	7722.3
15°	7524.9
16°	7346.9
17°	7172.7
18°	7010.1
19°	6851.4
20°	6708.2
21°	6561.1
22°	6410.1
23°	6278.5
24°	6131.5
25°	5957.2
26°	5763.7
27°	5539.2
28°	5299.2
29°	5032.1
30°	4737.9
31°	4405.0
32°	4060.6
33°	3700.6
34°	3332.8
35°	2976.6
37.5°	2101.8
40°	1354.7
42.5°	797.4
45°	452.9
47.5°	243.9
50°	123.9
52.5°	23.2
55°	7.8
57.5°	3.9



TEST NUMBER: P250614

CATALOG NUMBER: LD8B150D010 ER8B150927 8LBM0B

**CANDELA DISTRIBUTION (continued):**

	0°
60°	0.0
62.5°	0.0
65°	3.9
67.5°	0.0
70°	0.0
72.5°	3.9
75°	0.0
77.5°	0.0
80°	3.9
82.5°	0.0
85°	0.0
87.5°	3.9
90°	0.0

(END OF REPORT)