

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P249633

Luminaire Tested: **LD8B200D010 ER8B200840 8LBS0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P249633
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-95)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B200D010 ER8B200840 8LBS0GPH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 4000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 21359.0 lumens
Efficiency: N/A
Efficacy: 95.7 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.22
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 223.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P249633

CATALOG NUMBER: LD8B200D010 ER8B200840 8LBS0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P249633

CATALOG NUMBER: LD8B200D010 ER8B200840 8LBS0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81
3	98	90	84	79	96	88	83	78	85	81	77	83	79	75	81	77	74	72
4	91	82	75	69	89	80	74	69	78	73	68	76	71	67	74	70	66	65
5	85	75	67	62	83	73	67	62	72	66	61	70	64	60	68	63	60	58
6	79	68	61	56	78	67	60	55	66	59	55	64	59	54	63	58	54	52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47
8	69	58	51	45	68	57	50	45	56	50	45	55	49	45	54	49	45	43
9	65	54	46	42	64	53	46	41	52	46	41	51	45	41	50	45	41	39
10	61	50	43	38	60	49	43	38	48	42	38	47	42	38	47	41	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	378210
5°	377569
10°	376223
15°	373234
20°	367820
25°	359325
30°	346147
35°	326834
40°	297924
45°	243077
50°	175878
55°	111023
60°	59607
65°	27012
70°	9178
75°	4563
80°	3054
85°	1415



TEST NUMBER: P249633

CATALOG NUMBER: LD8B200D010 ER8B200840 8LBS0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1158.6	5.4
10°-20°	3294.1	15.4
20°-30°	4850.9	22.7
30°-40°	5401.1	25.3
40°-50°	4265.7	20.0
50°-60°	1912.5	9.0
60°-70°	422.1	2.0
70°-80°	47.6	0.2
80°-90°	6.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	9303.7	43.6
0°-40°	14704.7	68.8
0°-60°	20883.0	97.8
0°-90°	21359.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	21359.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12265	
5°	12198	###
15°	11691	3294
25°	10561	4851
35°	8682	5401
45°	5574	4266
55°	2065	1912
65°	370	422
75°	38	48
85°	4	6
90°	0	



TEST NUMBER: P249633

CATALOG NUMBER: LD8B200D010 ER8B200840 8LBS0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	12265.1
2.5°	12246.6
5°	12197.7
7.5°	12122.3
10°	12015.3
12.5°	11871.1
15°	11691.3
17.5°	11471.9
20°	11208.8
22.5°	10906.0
25°	10560.9
27.5°	10163.0
30°	9721.4
32.5°	9215.0
35°	8682.2
37.5°	8109.8
40°	7401.1
42.5°	6524.6
45°	5574.0
47.5°	4606.2
50°	3666.2
52.5°	2806.8
55°	2065.1
57.5°	1442.4
60°	966.5
62.5°	612.1
65°	370.2
67.5°	206.2
70°	101.8
72.5°	55.5
75°	38.3
77.5°	27.8
80°	17.2
82.5°	9.3
85°	4.0
87.5°	1.3
90°	0.0

(END OF REPORT)